

Eaton's Arrow Hart
X-Switch motor controllers & disconnect switches

X-Switch motor controllers & disconnect switches

Arrow Hart

EATON

Powering Business Worldwide

Eaton's Arrow Hart X-Switch motor controllers & disconnect switches



AHDS30SSR



AHDS30SSR (Inside)

Motor Control Disconnect X-Switches

Product description

3-pole, 3-phase
NEMA 4X, 12 & IP66, IP69K
30A, 60A or 100A, 600V/AC max.

Features

- Compact NEMA 4X, NEMA 12, IP66 & IP69K rated, stainless steel enclosure is ideal for washdown environments
- NSF Listed for food processing areas
- Sloped enclosure enhances wash down & water run off
- High-visibility red handle can be padlocked to meet OSHA lockout/tagout requirements
- Retained, Tri-Combo screws for easy access
- Mounting feet provide full 1/4" clearance from mounting surface
- Optional breather drain prevents interior condensation buildup
- Expanded silicone gasket for superior ingress protection and easy cleaning
- Heavy-duty rotary disconnect switches designed for long life
- Auxiliary contacts are available for PLC or VFD applications
- Enclosure assembly made of 316L stainless steel for increased corrosion resistance

Common X-Switch Configurations

Catalog No.	Description	Amp
<input type="checkbox"/> AHDS30SSR	Motor Control Disconnect X-Switch, NEMA 4X	30
<input type="checkbox"/> AHDS60SSR	Motor Control Disconnect X-Switch, NEMA 4X	60
<input type="checkbox"/> AHDS100SSR	Motor Control Disconnect X-Switch, NEMA 4X	100
<input type="checkbox"/> AHDS30RS	Replacement switch	30
<input type="checkbox"/> AHDS60RS	Replacement switch	60
<input type="checkbox"/> AHDS100RS	Replacement switch	100
<input type="checkbox"/> AHDS30RAC	Aux contact - PLC	30
<input type="checkbox"/> AHDS30RVFD	Aux contact - VFD	30
<input type="checkbox"/> AHDS60RAC	Aux contact - PLC	60
<input type="checkbox"/> AHDS60RVFD	Aux contact - VFD	60
<input type="checkbox"/> AHDS100RAC	Aux contact - PLC	100
<input type="checkbox"/> AHDS100RVFD	Aux contact - VFD	100
<input type="checkbox"/> AHDS30CH	X-Switch Conduit Hub, Size 3/4"	For 30A Enclosure
<input type="checkbox"/> AHDS60CH	X-Switch Conduit Hub, Size 1-1/4"	For 60A Enclosure
<input type="checkbox"/> AHDS100CH	X-Switch Conduit Hub, Size 2"	For 100A Enclosure
<input type="checkbox"/> AHDSBD	Breather Drain IP69K rated	—
<input type="checkbox"/> AHDS30RTCASSR	Replacement top cover assembly	For 30A Enclosure
<input type="checkbox"/> AHDS61RTCASSR	Replacement top cover assembly	For 60/100A Enclosure

Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/arrowhart

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/arrowhart

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 17.8 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, Mexico CP 54800
México
Eaton.mx
Eaton.com/arrowhart