

Eaton's Arrow Hart
TR Extra heavy-duty receptacles

Arrow Hart

TR Extra heavy-duty
receptacles meet TR code
requirements in the most
demanding environments



EATON

Powering Business Worldwide

Eaton's tamper resistant, extra heavy-duty receptacles are available in a number of styles, from standard and decorator, to spec and hospital grade. The tamper resistant duplex receptacles are back and side wire-able for convenience and are available in 15A or 20A, 125V.



Design features

- Tamper resistant receptacles provide compliance with 2014 NEC® Article 406.12 which states that all 15A and 20A, 125V/AC receptacles installed in dwelling units must be tamper resistant
- Exclusive screw terminal guards provide fast, easy insulation from conductive surfaces
- Exclusive five-leaf solid brass line contacts provides consistent performance and superior plug retention
- Long, broad mounting strap helps reach large panel cutouts for code compliance
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper used
- Screw-catch feature on duplex devices speeds mounting of wallplates
- "TR" designation provides visual identification

TR Extra heavy-duty receptacles



Catalog no.	Description	Amps	V/AC	Color suffix
<input type="checkbox"/> AHTR5262__	Tamper resistant duplex receptacle with terminal guards	15	125	B, BK, GY, RD, V, W
<input type="checkbox"/> AHTR5362__	Tamper resistant duplex receptacle with terminal guards	20	125	B, BK, GY, LA, RD, V, W
<input type="checkbox"/> AHTRIG5262__	Tamper resistant isolated ground duplex receptacle	15	125	GY, RD, RN, V, W
<input type="checkbox"/> AHTRIG5362__	Tamper resistant isolated ground duplex receptacle	20	125	BK, GY, RD, RN, V, W
<input type="checkbox"/> AHTR8200__	Hospital grade tamper resistant duplex receptacle with terminal guards	15	125	B, GY, RD, V, W
<input type="checkbox"/> AHTR8300__	Hospital grade tamper resistant duplex receptacle with terminal guards	20	125	B, BK, GY, LA, RD, V, W
<input type="checkbox"/> TR8262__	Hospital grade tamper resistant decorator duplex receptacle	15	125	GY, RD, V, W
<input type="checkbox"/> TR8362__	Hospital grade tamper resistant decorator duplex receptacle	20	125	B, BK, GY, RD, V, W
<input type="checkbox"/> TRIG8262__	Hospital grade tamper resistant isolated ground decorator duplex receptacle	15	125	GY, RD, V, W
<input type="checkbox"/> TRIG8362__	Hospital grade tamper resistant isolated ground decorator duplex receptacle	20	125	GY, RD, V, W
<input type="checkbox"/> TRIG8200__	Hospital grade tamper resistant isolated ground duplex receptacle	15	125	GY, RD, RN, V, W
<input type="checkbox"/> TRIG8300__	Hospital grade tamper resistant isolated ground duplex receptacle	20	125	GY, RD, RN, V, W



AHTR8200



TR8362




AHTRIG5262



TRIG8300

Color ordering information

B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), RN (Orange), V (Ivory), W (White)



Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/arrowhart

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/arrowhart

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 178 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, Mexico CP 54800
México
Eaton.mx
Eaton.com/arrowhart