

# SIHAZYM™ Panzym™ Enzyme Navigator



ENZYMES



*Powering Business Worldwide*


## Must Clarification & Mash Extraction

The process of using wine enzymes is simple and gentle in many stages of wine production. Areas of

application for wine enzymes include must clarification, mash extraction, aroma release in white wines, and

filtration improvement. Wine enzymes weren't invented by industry. Naturally occurring wine enzymes served as the

basis for development of more efficient enzymes in higher concentrations.



### Must clarification: natural and gentle with SIHAZYM Claro enzyme


Must clarification plays a key role in speeding the fermentation of grape must with the complete break down of pectin. Grape must can be clarified quickly and effectively with the aid of SIHAZYM Claro enzyme, either through flotation or sedimentation.

SIHAZYM Claro enzyme is a highly active, pectolytic must clarification enzyme. It enables very fast must clarification at a low dosage. Use 1 – 1.5 g/hl at approx. 15 °C in order to obtain pectin-free, clarified must within two to four hours. At must temperatures of approx. 10 °C, a dosage of 2 g/hl has the desired effect within two

hours. During enzymatic clarification of cold grape must SIHAZYM Claro enzyme (4 g/hl at  $\geq 5$  °C) speeds up sedimentation. Since the enzyme is active up to 1,000 mg/l  $\text{SO}_2$ , common grape/must sulphurization (20 – 50 mg/l  $\text{SO}_2$ ) is possible.

#### Benefits:

- Fast, gentle and natural must clarification
- Preservation of aroma precursors
- No input of oxidation, reductive operation possible
- High clarifying level, low NTU levels
- Sixty percent lower sediment than non-treated musts



### Mash extraction: increase juice and colour yield with SIHAZYM Extro enzyme


The pulp of grapes cells contains mainly natural, pectolytic enzymes. During maturation they aid continuous growth of the pulp cells. At the end of the maturation they are located in the grape skin and transfer to the mash during the subsequent grape extraction. Their natural enzyme activity is inhibited through this transition, the low pH value, and low or excessive mash temperatures.

SIHAZYM Extro enzyme enhances the natural enzyme activities, resulting in optimal mash extraction. In addition to pectinlyases, it contains pectinesterases and polygalacturonases as an enzyme complex and is therefore

ideally adapted to the specific oenological requirements. SIHAZYM Extro enzyme is effective in a wide pH range between 2.9 and 4.0 and large temperature range (10 – 60 °C).

#### Benefits:

- Highly active enzyme for both white and red mash
- Faster and more effective break down of residual pectins
- Fast sedimentation, low NTU content
- Fast must clarification
- Increased proportion of free-run grape must
- Increased aroma and color extraction



**Filtration improvement: gentle and simple break down of filtration-inhibiting substances with SIHAZYM Fine and SIHAZYM Wine Clear enzymes**


Filtration problems can be ascribed to the state of health of the grapes. The main filtration-inhibiting substance is  $\beta$ -glucan, which is produced by *Botrytis cinerea* on the grapes. This inhibitor can cause filtration problems from 0.6 mg/l. The only way to break down  $\beta$ -glucan is to use  $\beta$ -glucanase, which is contained in SIHAZYM Fine enzyme.

SIHAZYM Wine Clear enzyme can be used in grape mashes and during alcoholic fermentation. It accelerates wine

clarification and increases wine filterability due to the combination of pectolytic and  $\beta$ -glucanase enzyme activities.

**Benefits:**

- Improves filtration of grapes affected by botrytis
- Simplifies fining and clarification of the wines
- Reliably breaks down pectin and filtration-inhibiting substances




**General application: must clarification and mash extraction with SIHAZYM Uni enzyme**

SIHAZYM Uni enzyme is a special enzyme combination for must clarification and mash extraction. A dosage of 3 g/hl at approx. 15 °C during must clarification results in pectin breakdown and clarification of the grape must within four to ten hours. For mash extraction dosages of 3 – 4 g/100 kg of mash are required, in order to achieve improved process yield, i.e., more free-run must.

**Benefits:**

- Wide action spectrum
- Fast must clarification with low NTU levels
- Higher quantity of free-run must
- Enhanced extraction of pigments (anthocyanins)



## Monoterpene release: re- lease of odor-active aromas with SIHAZYM A enzyme

In aroma-intensive, white wines a variety of flowery aromas are bonded in the grape skin. These  $\beta$ -glucosidically-bonded aromas transfer to the wine after pressing and fermentation. The application of SIHAZYM A enzyme releases the odor-active aromas and makes them sensorially noticeable for the wine taster.

SIHAZYM A enzyme is optimized for white wine applications. Since the enzyme is inhibited by must sugar, it cannot release the aroma substances until after the alcoholic fermentation. It should therefore be used at the young wine stage. After the required reaction time, it


should be deactivated through bentonite fining.

Since SIHAZYM A enzyme splits pigments, resulting in decolorization, it should not be used in red wine.

### Benefits:

- Releases monoterpenes in white wines
- Increases the content of flowery aromas
- High  $\beta$ -glucosidase activity
- Temperature range > 16 °C





**Mash extraction  
Rosé wine preparation with  
Panzym Rosé**

Enzymes are required for specific and fast depectinization in the preparation of rosé wine. An enzymatic breakdown during the pressing of the „rosé mash“ results in gentle juice extraction, i.e. an increase in the proportion of free-running must. The high polygalacturonase activity of Panzym Rosé additionally protects against over-extraction and improves the color stability of the rosé. Panzym Rosé is optimized for use in rosé mashes.

Benefits:

- More free-running must
- No over-extraction
- Gentle processing up to 5°C



## Application Table

Enzyme	Application – wine production stage	Use in	Temperature	
<b>SIHAZYM Claro</b>	Must stage	Clarification tank, flotation, sedimentation	Must clarification: sedimentation	approx. 10 °C
			Must clarification: sedimentation	approx. 15 °C
			Flotation	approx. 15 °C
<b>SIHAZYM Extro</b>	Mash stage	Mash transport, mash maceration time, mash fermentation, re-cooled mash (approx. 50 °C)	White and red mash	8 – 18 °C
			White and red mash	18 – 25 °C
			Conventional red wine mash fermentation	15 – 25 °C
			Flash pasteurization	30 – 40 °C
<b>SIHAZYM Fine</b>	End of fermentation, yeast storage, extraction of mannoproteins	Fermentation tank, young wine storage	Grapes affected by botrytis, fermentation tank	approx. 16 °C
			Abating fermentation	> 16 °C
			Yeast storage, mannoproteins	> 16 °C
			Difficult to filter young wines	> 16 °C
<b>SIHAZYM Wine Clear</b>	Mash stage, end of fermentation	Mash transport, mash maceration time, mash fermentation, re-cooled mash (approx. 50 °C), alcoholic fermentation	White wine mash	approx. 15 °C
			Re-cooled mash	approx. 15 °C
			Musts difficult to clarify	> 16 °C
			Grapes affected by botrytis	approx. 16 °C
<b>SIHAZYM Uni</b>	Must and mash stage	Mash transport, mash maceration time, mash fermentation, re-cooled mash (approx. 50 °C), clarification tank, flotation, sedimentation	White wine mash	12 – 15 °C
			Conventional red wine mash fermentation	18 – 20 °C
			Re-cooled mash	approx. 50 °C
			Must clarification: sedimentation	approx. 15 °C
			Difficult to filter young wines	approx. 16 °C
<b>SIHAZYM A</b>	Release of monoterpenes, young wine stage, only for white wines	Storage tank	Young wine with yeast storage	> 16 °C
			Young wine without yeast storage	> 16 °C
<b>Panzym Rosé</b>	Rosé mash stage	Mash transport, cold maceration (5°C), press	Rosé wine grapes	5 – 20 °C
			Rosé wine mashes	5 – 20 °C
			Recooled mash	approx. 60 °C



Dosage	Time	Cinnamyl esterase activity	Product formulation	Production process
2 g/hl	2 – 6 hours	Cleaned, free	Granulate	Combination of solid-phase and submers method
1 – 1.5 g/hl	2 – 4 hours			
2 g/hl	0.5 – 1 hour			
3 g/100 kg	4 hours – 2 days	Cleaned, free	Granulate	Submers method
2 g/100 kg	5 – 20 days			
2 – 3 g/100 kg	5 – 20 days			
2 g/100 kg	0.5 – 6 hours			
3 – 5 g/hl		Cleaned, free	Granulate	Combination of solid-phase and submers method
2 – 3 g/hl	8 – 14 days			
2 – 3 g/hl	Up to 21 days			
5 – 8 g/hl	Up to 8 days			
3 – 5 g/100 kg	4 – 6 hours	Cleaned, free	Granulate	Submers method
3 – 5 g/100 kg	4 – 6 hours			
3 – 4 g/100 kg	4 – 6 hours			
3 – 7 g/100 kg				
3 – 4 g/100 kg	2 – 4 hours	Cleaned, free	Granulate	Combination of solid-phase and submers method
3 – 5 g/100 kg	5 – 20 days			
2 g/100 kg	2 – 4 hours			
3 g/hl	4 – 10 hours			
2 g/hl (+ SIHAZYM Fine 3 g/hl)	2 – 6 hours			
4 – 6 g/hl	2 – 8 weeks	Weak	Granulate	Combination of solid-phase and submers method
3 – 5 g/hl	1 – 2 weeks			
2 – 4 ml/100 kg	1 – 2 hours	Low	Liquid	Submers method
2 – 3 ml/100 kg	1 – 2 hours			
1 – 2 ml/100 kg	1 – 2 hours			





Powering Business Worldwide

#### North America

44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

#### Europe/Africa/Middle East

Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

Friedensstraße 41  
68804 Altlussheim, Germany  
Tel: +49 6205 2094-0

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

#### China

No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

#### Singapore

4 Loyang Lane #04-01/02  
Singapore 508914  
Tel: +65 6825-1668

#### Brazil

Rua Clark, 2061 - Macuco  
13279-400 - Valinhos, Brazil  
Tel: +55 11 3616-8400

**For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)**

© 2017 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

EN  
1 B 1.6.4.1  
05-2017