


SIHA[®] Yeast Navigator




EATON

Powering Business Worldwide

White wine grape varieties:



Red wine grape varieties:



Overview White Wine Yeasts

White wine yeasts					
Name	Selection	Particularly suitable for	Dosage	Character/ Characteristics	Fermentation
SIHA Active Yeast 3 <i>Saccharomyces Cerevisiae</i>	Wine region Nahe, Germany	Silvaner, Müller-Thurgau, Pinot Blanc, Pinot Gris, Portugieser, Grüner Veltliner	15 – 20 g/hl, 40 g/hl under unfavorable conditions	For fruity white and red wines, prime character in red wines	Prefers musts with balanced nutrient content, FAN: ≥ 200 mg/l, fermentation temperature: 15 – 22 °C
SIHA Active Yeast 7 (Riesling Yeast) <i>Saccharomyces Cerevisiae</i>	Wine region Palatinate, Germany	Riesling, Müller-Thurgau, Muscat varieties, Gewürztraminer, Sauvignon Blanc, Semillion Blanc	15 – 20 g/hl, 30 g/hl under unfavorable conditions	Increased β-glucosidase activity, promotes citrus, tropical fruit, and pineapple aromas	High final degree of fermentation, fermentation temperature: 15 – 20 °C
SIHA VARIOFERM <i>Saccharomyces Cerevisiae</i>	Wine regions Rheingau, Rheinhessen, Nahe, Germany	Riesling, Chardonnay, Pinot Blanc, Pinot Gris, Ribolla, Tocai	15 – 20 g/hl, max. 30 g/hl under unfavorable conditions	3 <i>Saccharomyces Cerevisiae</i> strains, peach and passion fruit aromas, complexity and aroma variety, used for long Bâtonnage	Rather slow fermentation, prefers high quality musts, Important: NTU: > 70, prefers musts with balanced nutrient content, FAN: ≥ 220 mg/l fermentation temperature: 15 – 18 °C
SIHA CRYAROME <i>Saccharomyces Cerevisiae</i>	Wine region Sauterne, France	Sauvignon Blanc, Riesling, Müller-Thurgau, Silvaner, Muscatel, Welschriesling, new genetically diverse varieties	15 – 20 g/hl, 20 – 25 g/hl at ≤ 15 °C	„The Sauvignon Blanc yeast“, high β-lyase activity, increased formation of fatty acid esters, excellent cold fermentation characteristics	Preferred temperature 15 °C, minimum 13 °C, FAN: ≥ 150 mg/l, fermentation temperature: 13 – 18 °C
SIHA WhiteArome <i>Saccharomyces Cerevisiae</i>	Wine region Mosel, Germany	Riesling, Pinot Blanc, Pinot Gris, Gutedel, Muscat varieties, Traminer, Malvasia	15 – 20 g/hl, 25 – 30 g/hl under unfavorable conditions	For harmonic white wines with good, grape variety-specific fruit aromas	Fermentation temperature: 18 – 20 °C
SIHAFERM PureNature	<div style="display: flex; justify-content: space-around;"> <div style="border: 1px solid black; padding: 2px; font-size: 8px;"> SIHAFERM Pure <i>Saccharomyces Cerevisiae</i> </div> <div style="border: 1px solid black; padding: 2px; font-size: 8px;"> SIHAFERM Nature <i>Torulaspota Delbrueckii</i> </div> </div> <p><i>Saccharomyces Cerevisiae</i>: Wine region Württemberg, Germany</p> <p><i>Torulaspota Delbrueckii</i>: Wine region Rheingau, Germany</p>	Riesling, Pinot Gris, Pinot Blanc, Silvaner, Chardonnay	Start of fermentation: 20 g/hl SIHAFERM Nature, after 15 °Oe decrease add 20 g/hl SIHAFERM Pure	Imitation of spontaneous fermentation, SIHAFERM Nature: low volatile acidity, low alcohol yield, synthesis of fruity ester, SIHAFERM Pure: high final degree of fermentation, neutral aroma	Medium-speed fermentation with SIHAFERM Nature, speedy fermentation with SIHAFERM Pure, fermentation temperature: 15 – 20 °C, must-free SO ₂ : < 10 mg/l
SIHAFERM Frio <i>Saccharomyces Cerevisiae</i>	Wine region Rheinhessen, Germany	Chardonnay, Silvaner, Riesling, domestic grape varieties	20 – 25 g/hl, 30 g/hl under unfavorable conditions	Good cold fermentation characteristics, Killer “neutral”	Fast start of fermentation, alcohol tolerance up to 15 vol.-%, fermentation temperature: 12 – 23 °C
SIHAFERM Element <i>Saccharomyces Cerevisiae</i>	Wine region Palatinate, Germany	Riesling, Pinot Gris, Pinot Blanc, Chardonnay	20 – 25 g/hl, 30 g/hl under unfavorable conditions	Promotes grape variety-specific aroma, β-glucosidase activity, aroma: Flint, citrus	Moderate fermentation, alcohol tolerance up to 14.5 vol.-%, fermentation temperature: 17 – 22 °C

+++ strongly positive, ++ very positive, + positive, o neutral, – negative, – – very negative, – – – strongly negative

SIHA SpeedFerm™ for rehydration	SIHA Fermentation Salt (g/hl) max. 100 g/hl	SIHA PROFERM™ Plus (g/hl) max. 40 g/hl	Influence on MLF
++	15 – 20	20 – 40	++
+	20 – 30		---
++	20	40	++
++	15 – 25	10	0
+	20 – 30		+
+		20	0
++	50	20	0
+	30	20	+



Overview Sparkling Wine and Red Wine Yeasts

Sparkling wine yeasts

Name	Selection	Particularly suitable for	Dosage	Character/Characteristics	Fermentation
SIHA Active Yeast 4 <i>Saccharomyces</i> <i>Bayanus</i>	Wine region Champagne, France	Riesling, Pinot Blanc, Chardonnay, Pinot Noir	20 – 30 g/hl, 40 g/hl under unfavorable conditions	Apple and nut aromas, emphasizes fruity Champagne types, fine mousseux, very pressure tolerant	Very strong fermentation, high temperature tolerance, generates little acetaldehyde, fermentation temperature: 10 – 18 °C

Red wine yeasts

Name	Selection	Particularly suitable for	Dosage	Character/Characteristics	Fermentation
SIHA Active Yeast 8 (Burgundy Yeast) <i>Saccharomyces</i> <i>Cerevisiae</i>	Wine region Baden, Germany	Pinot Noir, Merlot, Pinotage, Pinot Meunier, St. Laurent, Zweigelt	15 – 20 g/hl, 30 g/hl under unfavorable conditions	Increased glycerin formation, dark fruit aromas such as blackberry, red currant, cherry, classic "Pinot type," low β -glucosidase activity, Killer „positive”, increased tannin extraction	Uniform, fast fermentation, tolerates nutrient-poor musts, alcohol tolerance up to 16 vol.-%, FAN: < 120 mg/l, fermentation temperature: 20 – 28 °C
SIHA Active Yeast 10 (Red Roman) <i>Saccharomyces</i> <i>Cerevisiae</i>	Wine region Piedmont, Italy	Dornfelder, Lemberger, Cabernet Sauvignon, Merlot, Cabernet Franc, Sangiovese, Syrah, Shiraz, Zinfandel, Refosco, Amarone, Nebbiolo	15 – 20 g/hl, max. 30 g/hl under unfavorable conditions	Spicy aromas, dark chocolate, autolysis capabilities, excellent for barrique vinification	Fast fermentation, temperature tolerance up to 32 °C, alcohol tolerance up to 16 vol.-%, fermentation temperature: 15 – 28 °C
SIHA Rubino Cru <i>Saccharomyces</i> <i>Cerevisiae</i>	Hybrid yeast	Cabernet Sauvignon, Pinot Meunier, rosé wine production	15 – 20 g/hl, max. 30 g/hl under unfavorable conditions	Mocha and dark chocolate aromas, color stability, Killer "positive"	Moderate fermentation, secure fermentation, alcohol tolerance up to 15.5 vol.-%, fermentation temperature: 18 – 25 °C
SIHAFERM Finesse Red <i>Saccharomyces</i> <i>Cerevisiae</i>	Wine region Württemberg, Germany	Pinot Noir, Cabernet Sauvignon, Merlot, Syrah, Zinfandel	15 – 20 g/hl	High stabilization of color by colorless polyphenols, spicy red wines	High fermentation activity, alcohol tolerance up to 15.5 vol.-%, fermentation temperature up to 30 °C

+++ strongly positive, ++ very positive, + positive, o neutral, – negative, -- very negative, --- strongly negative

SIHA SpeedFerm for rehydration	SIHA Fermentation Salt (g/hl) max. 100 g/hl	SIHA PROFERM Plus (g/hl) max. 40 g/hl	Influence on MLF
+	5 – 10		---

SIHA SpeedFerm for rehydration	SIHA Fermentation Salt (g/hl) max. 100 g/hl	SIHA PROFERM Plus (g/hl) max. 40 g/hl	Influence on MLF
+	10		++
++	10	20	+++
+		10	++
+		15 – 20	





Powering Business Worldwide

North America

44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Europe/Africa/Middle East

Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Friedensstraße 41
68804 Altlussheim, Germany
Tel: +49 6205 2094-0

An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

China

No. 3, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Singapore

4 Loyang Lane #04-01/02
Singapore 508914
Tel: +65 6825-1668

Brazil

Av. Julia Gaioli, 474 – Bonsucesso
07251-500 – Guarulhos, Brazil
Tel: +55 11 2465-8822

**For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration**

© 2015 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

EN
1 B 2.2.1.3
11-2015