

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST  
CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE  
CERTIFICATS D'ESSAIS DES EQUIPEMENTS  
ELECTRIQUES (IECEE) METHODE OC

**CB TEST CERTIFICATE****CERTIFICAT D'ESSAI OC**

Product  
Produit

Power Distribution System

Name and address of the applicant  
Nom et adresse du demandeur

Eaton Corp  
9650 Jeronimo Rd  
Irvine, CA 92618-2024 US

Name and address of the manufacturer  
Nom et adresse du fabricant

Eaton Corp  
9650 Jeronimo Rd  
Irvine, CA 92618-2024 US

Name and address of the factory  
Nom et adresse de l'usine

PHOENIXTEC ELECTRONICS (SHENZHEN) CO LTD  
6-7 FL BLDG 19 & BLDG 16, SHATOUJIAO FREE TRADE  
ZONE, SHENZHEN, GUANGDONG  
518081 CHINA

Note: When more than one factory, please report on page 2  
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2<sup>eme</sup> page

Additional Information on page 2  
See Page 2

Ratings and principal characteristics  
Valeurs nominales et caractéristiques principales

Trademark (if any)  
Marque de fabrique (si elle existe)

Eaton



Type of Manufacturer's Testing Laboratories used  
Type de programme du laboratoire d'essais  
constructeur

Model / Type Ref.  
Ref. De type

EMA6CCAAABA74AC, EMA6MG15EMH88AC,  
EMA6MT15JDD78AC, EMA6PAXXXXXXXXXX,  
EMA6PBXXXXXXXXXX, EMA6PCXXXXXXXXXX, See Page 2

Additional information (if necessary may also be  
reported on page 2)  
Les informations complémentaires (si nécessaire,,  
peuvent être indiqués sur la 2<sup>eme</sup> page

EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013.  
See Test Report for National Differences.  
 Additional Information on page 2

A sample of the product was tested and found  
to be in conformity with  
Un échantillon de ce produit a été essayé et a été  
considéré conforme à la

IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1, IEC  
60950-1(ed.2);am2

As shown in the Test Report Ref. No. which forms part  
of this Certificate  
Comme indiqué dans le Rapport d'essais numéro de  
référence qui constitue partie de ce Certificat

E94081-A47-CB-1 issued on 2014-08-01

This CB Test Certificate is issued by the National Certification Body  
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2014-08-04

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

**US-23699-UL**

**Model Details:**

EMA6PDXXXXXXXXXX,EMA6PEXXXXXXXXXX,EMA6XXXXXXXXXXXX Series,EMA7XXXXXXXXXXXX Series

Model abcdefghkmmnn where

a = branding, may be E or H

bb = intelligence level - may be MA, SW or MO

c = thermal rating may be 6 or 7

de = two digit input plug code. May be MA, MB, MC, MD, ME, MF, MG, MH, MJ, MT, MX, NJ, NT, PA, PB, PC, PD, PE, PF, PH, PJ, CA, CC, CE, CF, CH, CJ, CK, CL, CP, CX, DA, DB, DC, DD, DE, DF, DH, DJ, DK, DL, DM, DN, TA, TB, WF, WS, WU

f = power cable material and retention may be 1, 2, 3, 4, 5, 6, 7, 8, 9, A, B, D, E, H, J, L or M

g = variations in power cable length between 1m and 5m

h = circuit breaker type may be A, C, D, E, F, G, H, J, K or L

kk = two digit outlet configuration code. Two digit outlet config code. Refers to any combination of up to three types of outlets up to a maximum total socket count of 48.

mm = chassis may be 7x representing a 52x53mm chassis series between 902mm and 1829mm long or 8x representing a 52x65mm chassis series between 902mm and 1829mm long

nn = variations in product including presence of MOVs and others that do not affect safety such as color, firmware, mfr plant, or revision, may be alphanumeric, "-" or blank. See test report for details.

**Factories:**

PHOENIXTEC ELECTRONICS (SHEN ZHEN) CO LTD  
BLDG 16,SHATOUJIAO FREE TRADE ZONE,SHENZHEN,GUANGDONG  
518081 CHINA

EATON  
45 WEATHERS ST,YOUNGSVILLE NC  
27596 UNITED STATES

BERRECHID TECHNOLOGIES SARL  
Z.I LOT N°2, BD MOUAHIDINE,MA-26100 BERRECHID  
MOROCCO

**Ratings:**

EMA6CCAAABA74AC

Input: 100-240Vac, 2W+PE, 16 A, 50/60 Hz

EMA6MG15EMH88AC

Input: 100-127Vac, W+N+PE, 24 A, 50/60 Hz

EMA6MT15JDD78AC

Input: 200-240Vac, 2W+PE, 24 A, 50/60 Hz

EMA6PAXXXXXXXXXX

Input: 200-240Vac, 3W+PE, 16 A, 50/60 Hz

EMA6PBXXXXXXXXXX

Input: 120/208Vac, 3W+N+PE, 16 A, 50/60 Hz

EMA6PCXXXXXXXXXX

Input: 200-240Vac, 3W+PE, 24 A, 50/60 Hz

EMA6PDXXXXXXXXXX

Input: 120/208Vac, 3W+N+PE, 24 A, 50/60 Hz

EMA6PEXXXXXXXXXX

Input: 200-240Vac, 3W+PE, 35 A, 50/60 Hz

See test report for output rating details.

**Additional information (if necessary)**

**Information complémentaire (si nécessaire)**



UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2014-08-04

Signature:

Jolanta M. Wroblewska