

# Eaton 93PM 200 kW UPS

### Efficient, Scalable, Innovative,

The Eaton® 93PM UPS combines efficiency and reliability with an eye-catching design. A space-saving, scalable and flexible device that's as easy to deploy as it is to manage, it's the perfect three-phase white or grey space solution for today's data center.

# Lowest TCO (total cost of ownership)

- Conserve valuable data center floor space with the compact footprint, internal battery back-up and optional internal maintenance bypass
- Grow effortlessly with the vertical scalability, reducing cost and unexpected future growth risks
- Reduce power and cooling OPEX through industry-leading energy efficiency
  - 99 percent efficiency with Energy Saver System (ESS)
  - Up to 97 percent efficiency in double-conversion mode

### Easy deployment

Provides flexible configurability, maximizing deployment flexibility


# Easy management

- Track statistics on energy savings, battery time and outages profile your load and much more with the friendly graphical LCD touchscreen interface
- View system status from a distance with the green/ yellow/red LED light bars

## Advanced IT integration

- Supports optional communication cards that allow remote access via the HTTP(S), SNMP, MODBUS TCP/IP, Modbus RTU and BACnet IP protools
- Manage your power devices in your physical or virtual environment with Eaton's Power Xpert® software and Intelligent Power™ Software Suite
- Increase uptime through 24x7 remote monitoring and reporting capabilities using Eaton's PredictPulse™ service that alerts technicians during critical events and results in faster resolutions when a problem is detected; learn more at Eaton.com/PredictPulse

Eaton 93PM efficiency in doubleconversion and ESS





The 93PM ESS energy cost savings pay for the UPS in less than 3 years. Calculate your 93PM savings with ESS at **Eaton.com/ESS**.

# The functional core of the 93PM UPS

Top & bottom cable entry

Standard right-mounted wireway, supporting both top and bottom cable entry. This section contains all input and output connections for the UPS

- Communications and connectivity
  - Built-in device and host USB
  - Five alarm inputs and dedicated EPO
  - Alarm relay output
  - Four communication slots
- Color touchscreen LCD interface
- Serviceable redundant fan assembly
- Swappable power modules (50 kW) with independent control and power
- Soft start controls
- Static switch assembly





Open front view of the unit

Front view

#### EATON 93PM UPS TECHNICAL SPECIFICATIONS<sup>1</sup>

#### Power modules for 200 kW frame

with optional internal N+1 redundancy through 150 kW	Power offering (kW)	20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 120, 130, 140, 150, 160, 170, 180, 190, 200 kW with optional internal N+1 redundancy through 150 kW
---	---------------------	---

## **General characteristics**

Efficiency in Energy Saver System (ESS)	Up to 99%
Efficiency in double-conversion mode	Up to 97%
Parallel capability	Four distributed
Height x depth x width	74" x 42" x 32"

# Input characteristics

Voltage	480V 3-phase 3-wire or 4-wire (208V with IAC-D)
Voltage range	+10% / -15%
Frequency range	50/60 Hz
Power factor	> .99
Input current distortion	< 3% @ 100% load capacity

Battery voltage	432V, 48UV <sup>2</sup>
Charging method	ABM® or float technology

#### Output

Voltage	480V 3-phase 3-wire or 4-wire (208V with IAC-D)
Regulation	±1% steady state
Voltage THD	<1% (100% linear load); <5% (non-linear load)
Load power factor range	Unity with the ability to support 0.8 leading to 0.8 lagging without de-rating

#### Certification

Safety	UL 1778, UL 924 Auxiliary, cULus
EMC	FCC Part 15 subpart B class A
Surge	IEC 61000-4-5

#### **Optional accessories**

- Integrated slim maintenance bypass
  Integrated distribution cabinet (with output transformer options)
- Integrated power distribution cabinet
- Integrated battery cabinet (small and large)

# **UL 924 certification**

The 93PM meets the strict standards for UL 924 compliance for emergency lighting applications when ordered with an emergency lighting SKU. For more information, visit **Eaton.com/UL924UPS** 

<sup>1</sup>Due to continued improvements, specifications are subject to change. <sup>2</sup>480V battery voltage required for 480V 4-wire UPS configuration.

#### Eaton

1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

© 2018 Eaton All Rights Reserved Printed in USA BR153091EN / GG



Eaton, ABM, Intelligent Power, Power Xpert and PredictPulse are registered trademarks.

All other trademarks are property of their respective owners.

