



REVISIONS						
REV	CHG. NO.	ZONE	DESCRIPTION	DATE	BY	ENGR



CAD SYSTEM PRO/E DATABASE FER_1_8-3_1 PROPRIETARY INFORMATION IN THIS DOCUMENT IS THE EXCLUSIVE PROPERTY OF BEST POWER, UNIT OF GENERAL SIGNAL AND MAY BE USED SOLELY FOR INSTALLATION OR SERVICE OF BEST POWER'S PRODUCTS. ANY OTHER USE EXPRESSLY PROHIBITED. THIS DOCUMENT MUST NOT BE REPRODUCED WITHOUT BEST POWER'S WRITTEN PERMISSION AND MUST BE RETURNED TO BEST POWER UPON DEMAND.	DIMENSION TOLERANCE UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: INCHES ± DEC. DIM. XX = ± .02 DEC. DIM. XXX = ± .010 ANGLES ± 2°	APPROVED		BEST POWER A UNIT OF GENERAL SIGNAL P.O. BOX 280 NECEDAH, WI 54846 (608) 565-7200 TITLE: CENTER OF GRAVITY 3.1-1.8K RACKMOUNT	
		DRAWN BY: BEM DATE: 30-Nov-00	SIZE: B DWG NO:		REV: A
		CHECKED BY: BEM 11-30-00 ENGINEER: BEM 11-30-00 STANDARDS ENGINEER: RCM 11-30-00 MANUFACTURING ENG: WTB 11-30-00 QUALITY ASSURANCE: RJH 11-30-00	SCALE: 0.250 = 1.000		SHEET 1 OF 1
		DO NOT SCALE DRAWING	PART NO:		SHEET 1 OF 1