

Eaton FERRUPS UPS FE Series 60 Hz



Product Snapshot

Product rating:	500 VA–18 kVA
Input voltage	120/208/240, 208/240
Output voltage	120/208/240
Frequency:	60 Hz
Configuration:	Cabinet

Features

- Active voltage regulation converts power from almost any AC source into computer grade power
- Eliminates harmful harmonic currents from entering a building's wiring, where they can disrupt computer operations
- Enhanced diagnostics initiates automatic startup and scheduled tests on the logic board, battery and other critical systems
- Provides regulated output voltage without drawing power from batteries keeping the batteries full charged from unexpected blackouts
- Complete offering of LanSafe® power management software included to ensure data integrity
- Provides investment protection with a two-year limited warranty and a \$250,000 load protection guarantee (US and Canada)

Eaton® FERRUPS® uninterruptible power systems furnish unmatched reliability in configurable power protection for computers and telecommunications equipment. Patented ferroresonant technology delivers “bulletproof” power protection, overcoming spikes, sags, surges, noise and lightning. Eaton-exclusive SineSense provides clean, reliable power while conserving batteries during blackouts.

Extensive configurability options make FERRUPS the ideal power protection solution with a wide range of voltages, frequencies, runtimes, power cords and receptacles. FERRUPS prevents the backfeed of harmonic currents into building wiring which can disrupt computer operations.

Redundant power paths assure high fault-tolerance and optimum uptime. Galvanic isolation separates input from output, filtering line noise and surges. FERRUPS also features precision voltage regulation with no battery discharge down to 38% below nominal (depending upon load) as well as over 80 user-programmable diagnostic and communications functions.

FERRUPS models include free Eaton Software Suite power management software with connectivity cable and are BestLink SNMP/Web-ready for remote management. FERRUPS covers up to \$250,000 for damage to connected equipment resulting from a spike or surge (US and Canada only).



Powering Business Worldwide

FE SERIES, 60 HZ SPECIFICATIONS

Models	500 VA	700 VA	850 VA	1.15 kVA	1.4 kVA	1.8 kVA	2.1 kVA	3.1 kVA	4.3 kVA	5.3 kVA	7 kVA	10 kVA	12.5 kVA	18 kVA	
Part number	FE500 VA	FE700 VA	FE850 VA	FE1.15 kVA	FE1.4 kVA	FE1.8 kVA	FE2.1 kVA	FE3.1 kVA	FE4.3 kVA	FE5.3 kVA	FE7 kVA	FE10 kVA	FE12.5 kVA	FE18 kVA	
Capacity (kVA/kW)	.5/.35	.7/.5	.85/.6	1.15/.8	1.4/1	1.8/1.25	2.1/1.5	3.1/2.2	4.3/3	5.3/3.7	7/5	10/7.5	12.5/10	18/15	
Dimensions H x W x D	(inches)	12 x 10 x 21.25			15.1 x 15.2 x 20.2			21.2 x 15.25 x 22.9			29.5 x 15.5 x 25		36.5 x 19 x 32**		
	(mm)	305 x 255 x 540			385 x 390 x 515			540 x 390 x 585			750 x 395 x 635		930 x 485 x 815**		
Weight	(lb)	54	62	67	102	122	176	188	248	348	484	578	875	1089	1362
	(kg)	25	28	30	46	55	80	85	112	158	220	262	397	494	618
Input connection (hardwired input is standard for FE1.8 kVA and above)	6-ft cord w/NEMA 5-15P*					6-ft cord w/NEMA 5-20P*	6-ft cord w/NEMA L5-30P*	120V/40A 208V/25A 240V/20A	120V/50A 208V/30A 240V/25A	120V/70A 208V/40A 240V/35A	208V/60A 240V/50A	208V/80A 240V/70A	208V/110A 240V/100A		
Output connection	(4) NEMA 5-15R			(6) NEMA 5-15R		(6) NEMA 5-15R			Hardwired output is standard— for additional receptacle selections, refer to FERRUPS CTO Guide						
Typical runtime, minutes	(full load)	9	11	9	8	11	11	9	14	10	20	12	11	18	10
	(half load)	25	31	25	22	31	30	25	35	24	50	33	26	48	26

Operation

Nominal input voltage	120	120/208/240						208/240						
Input voltage range	+15%, -20%													
Input power factor	0.98													
Nominal output voltage	120	120/208/240												
Output voltage regulation	±3% for input voltages of +15% to -20%													
Output voltage waveform	Sine wave													
Output voltage THD	5% or less at rated kW load													
Overload capacity	150% surge and 125% for 10 minutes online, 150% surge and 110% for 10 minutes on inverter													
Transfer time	0 ms													
Lightning, surge & noise protection	2000:1 spike attenuation using ANSI/IEEE C62.41 and C62.45 Category A and Category B tests Common mode: >120 dB. Normal mode: >60 dB													
Efficiency	85	86	85	88	88	90	90	91	90	90	90	90	91	92
Safety certification	UL, CSA (cUL)													
EMI compliance	FCC Class A													
Testing standards	ANSI/IEEE C62.41 (1991); ANSI/IEEE C62.45 (2002); EN62040-2													
Communication	RS-232 serial port (DB25), plus contact closures													

Environmental

Operating temperature	0°C to 40°C (32°F to 104°F)													
Storage temperature	-20°C to +60°C (-4°F to 140°F)													
Relative humidity	5 to 95% without condensation													
Audible noise at 1m (dB)	41	41	47	49	49	51	51	51	50	51	54	61	61	61
Altitude	3,050m (10,000 ft) maximum													

Due to continuing product improvement programs, all specifications are subject to change without notice. *120V standard configuration. **Batteries in second cabinet. Contact factory for weights and dimensions.

To learn more about the Eaton FERRUPS UPS,
please visit: Eaton.com/Ferrups

Eaton
Electrical Sector
1000 Eaton Boulevard
Cleveland, OH 44122 USA
Eaton.com

Eaton.com/powerquality

© 2014 Eaton
All Rights Reserved
Printed in USA
BR153035EN
May 2014

Eaton, LanSafe and FERRUPS are registered trademarks of Eaton.

All other trademarks are property of their respective owners.

