

# FERRUPS Shipboard SEACOTS UPCS



These products are  
TAA Compliant

## Product snapshot

|                        |              |
|------------------------|--------------|
| <b>Product rating:</b> | 18 kVA       |
| <b>Input voltage:</b>  | 208/240V     |
| <b>Output voltage:</b> | 120/208/240V |
| <b>Frequency:</b>      | 60 Hz        |
| <b>Configuration:</b>  | Cabinet      |

## Features

- Meets stringent performance standards for installation in naval combatants
- Tested to MIL-S-901 and MIL-S-167-1
- Delivers bulletproof protection with ferroresonant technology
- Converts power from almost any AC source into computer-grade power
- Prolongs backup time with external battery cabinets
- Conditions incoming power without depleting the battery to preserve battery power for power outages
- Monitors internal logic board, batteries, and other critical components at scheduled intervals for reliable performance
- Saves money on installation costs by minimizing input breaker and wire size with low input THD and high power factor
- Ensures data integrity with complete offering of power management software

## FERRUPS SEACOTS rackmount model



## Product snapshot

|                        |               |
|------------------------|---------------|
| <b>Rating:</b>         | 3.1 kVA–5 kVA |
| <b>Input voltage:</b>  | 120V          |
| <b>Output voltage:</b> | 120V          |
| <b>Frequency:</b>      | 60 Hz         |
| <b>Configuration:</b>  | Rackmount     |

The FERRUPS® Shipboard Uninterruptible Power Conditioning System (UPCS) is uniquely designed to support nautical applications. After extensive development and testing, the FERRUPS performs reliably in the severe electrical and physical environment of naval combatants. Consisting of Shipboard Environmentally Adapted Commercial Off-the shelf (SEACOTS) components, the FERRUPS also meets TAA Compliant standards and is available on our GSA contract.

The FERRUPS essentially performs two main functions. First, it regulates incoming power, conditioning it so that the protected equipment connected to the UPCS always receives computer-grade power. This output power is consistently free from power disturbances that can cripple electronic warfare equipment. Both a sudden incident such as a violent surge and a long-term diet of poor quality power can damage electrical equipment on a naval vessel. Second, the FERRUPS contains batteries to provide power during a power outage. Should a power failure occur, the FERRUPS seamlessly switches to battery power without interruption. The FERRUPS can be fitted with multiple battery cabinets for extended battery backup time.

Backed by many years of reliable implementations and an unwavering commitment from Eaton to support Navy shipboard applications, the FERRUPS is a proven power protection system. The FERRUPS provides the highest level of design and performance to keep your critical applications running without interruption.



Powering Business Worldwide

## Computer-grade Power Conditioning and Regulation

The FERRUPS combines true, no-break regulated and conditioned computer-grade power with galvanic isolation. As a result, the effects of spikes, sags, surges, switching transients, and noise are eliminated without the addition of a separate power conditioner or isolation transformer. The FERRUPS converts power from almost any AC source, while its bi-directional filtering protects the ship's electrical power from electrical noise and harmonics generated by the protected equipment.

## Electrically Performance-Tested

The FERRUPS has been electrically performance-tested by the Naval Ship Systems Engineering Station on an ungrounded ship's power system in the land-based test site (LBTS). The FERRUPS meets the criteria for shipboard installation. The rugged FERRUPS has been medium weight shock-tested to MIL-S-901 (three "hits" each on all three axis) for Grade A unrestricted shipboard installation, and tested to MIL-S-167-1 through 50 Hz vibrations for unrestricted shipboard installation. The FERRUPS maintained all operational capabilities throughout the entire test evolution.

## Condition-based Maintenance, Self-diagnostics and Monitoring

The FERRUPS incorporates self-diagnostics that test and monitor its inverter, battery charger, logic, and operating limits. Should a system fail or exceed the operating limits, it alerts the user by sounding an audible alarm.

## Reliability

Since 1983, the FERRUPS with its patented ferroresonant technology continues to set the standard for reliable single-phase power protection. Now in its sixth generation, this state-of-the-art technology is at the core of each FERRUPS.

## Free Software

FERRUPS models include the free Software Suite CD with power management software and a connectivity cable. Free software upgrades and downloads are available on the Eaton Web site ([Eaton.com/powerquality](http://Eaton.com/powerquality)). The UPCS is equipped with an RS-232 communications port and status contact closures.



## Remote Monitoring

The FERRUPS can be directly interfaced to the ship's data network for remote monitoring with the optional BestLink Web/SNMP adapter, which provides SNMP, HTTP, SMTP, WAP, and Telnet compatibility as well as advanced RS-232 communications. The BestLink Web/SNMP adapter allows easy monitoring, management, and if necessary, safe shut down or reboot of equipment connected to the FERRUPS. The adapter expands your ability to control, track, and monitor power conditions throughout the network.



## BestLink Web/SNMP Adapter

## Compact Solution

All FERRUPS components fit through standard 26-inch x 66-inch ship hatches. Configured system packages include an external bypass, step-down transformer, and battery packs along with the UPCS itself.

## Service

The FERRUPS is backed by a 24/365 help desk and available on-site service. In addition, replacement parts can be shipped throughout the world, and operation and maintenance training are also available.

## Additional Battery Cabinets

The FERRUPS has multiple MIL-S-901 tested battery cabinets available for extended battery backup times.

## BATTERY BACKUP TIMES

|           | With Battery Pack<br>23FE-1295 | With Battery Pack 5FE-901-R<br>(rackmount model) |         |
|-----------|--------------------------------|--|---------|
|           | FE18kVA                        | FER 3.1  | FER 7.0 |
| Half Load | 1 hr. 46 min.                  | NA   | NA      |
| Full Load | 37 min.                        | 90 min   | 30 min  |

Note: Battery times are approximate and may vary with equipment, configuration, battery age, temperature, etc.

# TECHNICAL SPECIFICATIONS - TOWER MODEL<sup>1</sup>

## GENERAL

|                          |                                   |
|--------------------------|-----------------------------------|
| Part Number              | FE18kVA: FE18KINHAAAKL            |
| Power Rating             | 18 kVA / 15 kW                    |
| Input Connection         | Hardwired                         |
| Input Connection RatingA | FE18kVA: 208V / 105A, 240V / 100A |
| Output Connection        | Hardwired standard                |

## PHYSICAL

|                        |  |
|------------------------|--|
| Dimensions (H x W x D) | 36.5 x 19.0 x 32.0 in. / 930 x 485 x 815 mm  |
| Weight                 | FE18kVA: 1362 lb. / 618 kg   |
| Shock Mounts           | 6 shock mounts per UPS and 12 shock mounts per battery cabinet are required for Mil Spec 901 |

## OPERATION

|                                     |   |
|-------------------------------------|---|
| Nominal Input Voltage               | 208/240V  |
| Input Voltage Range                 | +15%, -20%  |
| Operating Frequency                 | 60 Hz   |
| Nominal Output Voltage              | 120/208/240V  |
| Output Voltage Regulation           | ±3% for input voltages of +15% to -20%  |
| Output Voltage Waveform             | Sine wave   |
| Output Voltage THD                  | 5% or less at rated kW load   |
| Overload Capacity                   | 150% surge and 125% for 10 minutes online, 150% surge and 110% for 10 minutes on inverter                                     |
| Transfer Time                       | 0 ms  |
| Nominal Battery Voltage             | 120 Vdc   |
| Lightning, Surge & Noise Protection | 2000:1 spike attenuation using ANSI/IEEE C62.41 and C62.45 Category A and B tests. Common mode: >120 dB. Normal mode: >60 dB. |
| Efficiency                          | FE18kVA: 92%  |
| Safety Certification                | UL, CSA (cUL)   |
| EMI Compliance                      | FCC Class A   |
| Testing Standards                   | MIL-S901, MIL-167-1, ANSI/IEEE C62.41 (1980); ANSI/IEEE 62.45 (1987); IEC 801-2, 801-4, 801-5                                 |
| Communication                       | RS-232 serial port (DB-25), plus contact closures   |

## ENVIRONMENTAL

|                          |  |
|--------------------------|--|
| Operating Temperature    | 0 to 40°C (32 to 104°F)  |
| Storage Temperature      | -20 to 60°C (-4 to 140°F)  |
| Relative Humidity        | 0 to 95% without condensation  |
| Audible Noise @ 1 meter  | FE18kVA: 57 dB   |
| Altitude                 | 3,050 m (10,000 ft.) maximum   |
| Front Panel Indicators   | AC Line: Status of AC input source<br>Ready: Availability of battery backup power<br>Charging: Status of battery charging<br>Battery Power: Illuminates when UPS is providing battery power<br>Alarm: General alarm status |
| Control Panel            | Keypad operation to change UPS modes and to display and change parameters  |
| Control Panel Connection | Attached to front of UPS with 6-ft. (1.8m) cable for hand-held operation   |

## BATTERY CHARGERS

|                |  |
|----------------|--|
| Dimensions     | Included within UPS enclosure                                  |
| Charger Rating | 20A  |
| Recharge Time  | Four times faster than standard, internal charger rated for 5A |

## OPTIONAL STEP-DOWN TRANSFORMERS

|               |  |
|---------------|--|
| Part Number   | FE18kVA: T2535183SNAVY                   |
| Voltage       | 480/240V in, 240V out; bulk head mounted |
| Qualification | Mil Spec 901 qualified                   |

## OPTIONAL BYPASS SWITCH

|               |                          |
|---------------|--------------------------|
| Part Number   | BPE05MBBAS1ALNVY         |
| Style         | Make-before-break switch |
| Qualification | Mil Spec 901 qualified   |

## OPTIONAL BATTERY PACK

|                        |  |
|------------------------|--|
| Part Number            | 23FE-1295  |
| Battery Description    | 2 strings of 100 Ah batteries, 10 batteries per string |
| Dimensions (H x W x D) | 50 x 29 x 32 in. / 1270 x 737 x 813 mm                 |
| Weight                 | 1910 lb. / 866 kg                                      |

1. Due to continuing product improvement programs, specifications are subject to change without notice.

# TECHNICAL SPECIFICATIONS - RACKMOUNT MODELS<sup>1</sup>

## GENERAL

|                          |   |
|--------------------------|---|
| Part Numbers             | FER3.1KDDAAAAAR*<br>FER3.1KDDEAAAAAR<br>FER7KDDFAAAFL |
| Power Ratings            | FER3.1: 3.1kVA/2.2kW<br>FER7: 5.0kVA/5.0kW            |
| Input Connection         | Hardwired   |
| Input Connection RatingA | FER3.1: 120V/35A<br>FER7: 120V/65A                    |
| Output Connection        | Hardwired standard                                    |

\*Internal battery

## PHYSICAL

|                        |   |
|------------------------|---|
| Dimensions (H x W x D) | FER3.1: 9.75x16x26.25 (inches)/<br>248x406x667(mm)<br>FER7.0: 19x16x26.25 (inches)/<br>483x406x667 (mm) |
| Weight                 | FER3.1*: 238 lb/108 kg<br>FER3.1: 138 lb/63 kg<br>FER7.0: 330 lb/150 kg                                 |

\*Internal battery model

## OPERATION

|                                     |  |
|-------------------------------------|--|
| Nominal Input Voltage               | 120V   |
| Input Voltage Range                 | +15%, -20%   |
| Operating Frequency                 | 60 Hz  |
| Nominal Output Voltage              | 120V   |
| Output Voltage Regulation           | ±3% for input voltages of +15% to -20%   |
| Output Voltage Waveform             | Sine wave  |
| Output Voltage THD                  | 5% or less at rated kW load  |
| Overload Capacity                   | 150% surge and 125% for 10 minutes online,<br>150% surge and 110% for 10 minutes on<br>inverter  |
| Transfer Time                       | 0 ms   |
| Nominal Battery Voltage             | 48 Vdc   |
| Lightning, Surge & Noise Protection | 2000:1 spike attenuation using ANSI/IEEE<br>C62.41 and C62.45 Category A and B tests.<br>Common mode: >120 dB.<br>Normal mode: >60 dB. |
| Efficiency                          | FER3.1: 91%<br>FER7: 90%   |
| Safety Certification                | UL, CSA (cUL)  |
| EMI Compliance                      | FCC Class A  |
| Testing Standards                   | MIL-S901, MIL-167-1, ANSI/IEEE C62.41<br>(1980);<br>ANSI/IEEE 62.45 (1987); IEC 801-2, 801-4, 801-5                                    |
| Communication                       | RS-232 serial port (DB-25), plus contact<br>closures   |

## ENVIRONMENTAL

|                         |   |
|-------------------------|---|
| Operating Temperature   | 0 to 40°C (32 to 104°F)   |
| Storage Temperature     | -20 to 60°C (-4 to 140°F)   |
| Relative Humidity       | 0 to 95% without condensation   |
| Audible Noise @ 1 meter | FER3.1: 52dB<br>FER7: 52 dB   |
| Altitude                | 3,050 m (10,000 ft.) maximum  |
| Front Panel Indicators  | AC Line: Status of AC input source<br>Ready: Availability of battery backup power<br>Charging: Status of battery charging<br>Battery Power: Illuminates when UPS is pro-<br>viding battery power<br>Alarm: General alarm status |

## OPTIONAL BYPASS SWITCH

|               |                          |
|---------------|--------------------------|
| Part Number   | BPE04MBBAS1ARML          |
| Style         | Make-before-break switch |
| Qualification | Mil Spec 901 qualified   |

## OPTIONAL BATTERY PACK

|                        |  |
|------------------------|--|
| Part Number            | 5FE-901-R  |
| Battery Description    | 1 string of 75 Ah batteries, 4 batteries per<br>string |
| Dimensions (H x W x D) | 10.5 x 19 x 26.5 in. / 268 x 482 x 673 mm              |
| Weight                 | 353 lb. / 160 kg                                       |

1. Due to continuing product improvement programs, specifications are subject to change without notice.

For more information, please visit  
[Eaton.com/MarineUSG](http://Eaton.com/MarineUSG)

**Eaton Corporation**  
Electrical Sector  
1111 Superior Avenue  
Cleveland, OH 44114 USA  
Eaton.com

© 2012 Eaton Corporation  
All Rights Reserved  
Printed in USA  
FER05FXA  
October 2012

Eaton is a registered trademark  
of Eaton Corporation.

All other trademarks are property  
of their respective owners.