





LTR	ECO No.	REVISION	DR	CK	AP	AP	DATE
A	NONE	ENGINEERING RELEASE	JK				08/19/05
B	8548	UPDATE CHASSIS & TEXT	LS		DK		20 FEB 08
C	11470	UPDATE EATON LOGOS	GS				18 MAY 10
002	064663	ADD ROHS NOTES	HN				30 APR 14



NOTES

- RACK MOUNTED STEEL CHASSIS, BLACK MEDIUM TEXTURE
19.00" WIDE STD. RACK MOUNT WITH ADJUSTABLE BRACKETS
1.72" HIGH
7.00" DEEP
UNIT REQUIRES CHASSIS SUPPORT BRACKETS
 - DUAL INPUT:
PRIMARY: 200-240 VAC 24A, SINGLE PHASE, 50/60HZ
CABLE: 10/3 SJOOW, 9 FOOT, NEMA L6-30 PLUG
SECONDARY: 200-240 VAC 24A, SINGLE PHASE, 50/60HZ
CABLE: 10/3 SJOOW, 9 FOOT, NEMA L6-30 PLUG
 - OUTPUT: 200-240 VAC 24 AMPS MAX 50/60HZ.
CABLE: 10/3 SJOOW, 3 FOOT, NEMA L6-30 OUTLET
 - FILTER: NONE
 - SPIKE SURGE PROTECTION: LINE TO LINE
 - CIRCUIT BREAKER: NONE
 - INDICATOR LIGHTS: FIVE
1 BLUE, ON WHEN THERE IS POWER TO OUTLETS
4 GREEN, DISPLAYS POWER AVAILABLE FROM DUAL SOURCE, AND IDENTIFIES THE SOURCE IN USE
 - AUTOSWITCH BETWEEN PRIMARY AND SECONDARY POWER SOURCE
- | INPUT VOLTAGE | DROP-OUT | PULL-IN |
|-----------------|----------|---------|
| 208 VAC SETTING | 182 | 195 |
- MINIMUM POWER FACTOR OF .85 LEADING OR LAGGING
 - UL RECOGNIZED COMPONENTS WHERE APPLICABLE.
 - RoHS COMPLIANT PER DIRECTIVE 2011/65/EU WITH APPLICABLE EXEMPTIONS.
 - ALL MATERIALS AND SUB-MATERIALS COMPLY WITH EATON SPECIFICATION 164080496. DOCUMENTATION CERTIFYING COMPLIANCE TO EATON SPECIFICATION 164080496 IS AVAILABLE UPON REQUEST.



NET XPERTS, LLC APPROVAL _____ DATE _____

THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERETO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2010 EATON CORP

EATON		9650 Jeronimo Road, Irvine, California 92618 Phone (949) 452-8500 www.ePDU.com	
DIMENSIONS IN INCHES TOLERANCES: DECIMALS .005 ANGLES .010 UNLESS OTHERWISE SPECIFIED CAGE CODE 51795		TITLE ENGINEERING DRAWING T2235-3358 ASSY 3358	
DRAWN BY: JK	DWG FILENAME: T_2235_3358_ME.DWG	SCALE: 1:1	SHEET: 1 OF 1
REV: 002	T_2235_3358_ME		