

# Eaton Power Xpert 9395P 300kVA/275kW UPS Technical Specification

Manufacturer's declaration in accordance with IEC 62040-3

IEC 62040-3 Subclause	MODEL RATING (0,9 p.f.)	300kVA
	Model catalogue reference	9395P-300
	UPS options	External battery cabinets System Bypass Module (SBM)
	External paralleling (HotSync technology)	Up to 5 units with distributed bypass Up to 7 units with centralized bypass
5.1.1	UPS topology	Double conversion, IGBT converters
5.3.4	UPS performance classification	VFI-SS-111

## MECHANICAL

	UPS dimensions (width x depth x height)	1350 x 880 x 1880 mm
	Weight, UPS	880 kg
	Large External Battery Cabinet dimensions (width x depth x height)	1125 x 808x 1879 mm
	UPS Cable entry	Top and Bottom entry
	UPS Degree of protection	IP 20
	UPS colour	Black; RAL 9005

## ENVIRONMENTAL

6.5.5	Acoustic noise at 1 m, in 25 °C ambient temperature	< 78dBA in double conversion, full load < 71dBA in double conversion, <65% load
4.1.4	Ambient UPS storage temperature range	- 25 °C to + 60 °C in the protective package
4.2.1.1 and 5.4.2.2 h	Ambient operating temperature range UPS Battery	0 °C to + 40 °C <i>No output power derating required.</i> The maximum rate of temperature change shall be limited to 1.67 °C over 5 minutes (20 °C/hour), based on the ASHRAE standard 90.1-2013  + 20 °C to + 25 °C recommended for optimized battery life time
4.2.1.1	Relative humidity range	5 to 95%, no condensation allowed There shall be at least a 1.0 °C difference between the dry bulb temperature and the wet bulb temperature, at all times, to maintain a non-condensing environment
4.2.1.2	Maximum service altitude	1000 m (3300 ft) above sea level Maximum 2000 m (6600 ft) with 1% derating per each add 100m

# Eaton Power Xpert 9395P 300kVA/275kW UPS Technical Specification

Manufacturer's declaration in accordance with IEC 62040-3

IEC 62040-3 Subclause	<b>MODEL RATING (0,9 p.f.)</b>	<b>300kVA</b>
--------------------------	--------------------------------	---------------

## EFFICIENCY

5.3.2 r and 6.4.1.6	Efficiency in double-conversion, rated linear load	100% load	95,5 %
		75% load	96,1 %
		50% load	96,3 %
		25% load	95,6 %
	Heat dissipation in double conversion	100% load	12,7 kW
		75% load	8.4 kW
		50% load	5,3 kW
		25% load	3,2 kW
		No load	2,3 kW
	Efficiency in ESS, rated linear load	100% load	99,3 %
		75% load	99,3 %
		50% load	99,2 %
		25% load	99,0 %

## ELECTRICAL CHARACTERISTICS

### INPUT

5.2.1.a and 5.2.1 b	Rated input voltage	220/380V; 230/400 V; 240/415 V	
	Voltage tolerance	Rectifier input	230 V -15% / +15%
		Bypass input	230 V -10% / +10%
5.2.1 c and 5.2.1 d	Rated input frequency	50 or 60 Hz, user configurable	
	Frequency tolerance	45 to 65 Hz	
5.2.2 a and 5.2.2 b	Number of input phases	3 phases	
		Rectifier input	3 phases + neutral
		Bypass input	
5.2.2 d	Input power factor, double conversion mode	25-100% load	> 0,99
		10-25% load	> 0,97
5.2.2 c	Rated input current	418 A r.m.s (400V)	

# Eaton Power Xpert 9395P 300kVA/275kW UPS Technical Specification

Manufacturer's declaration in accordance with IEC 62040-3

IEC 62040-3 Subclause	MODEL RATING (0,9 p.f.)	300kVA
5.2.2 f	Maximum input current	500A
5.2.2 h and 5.2.2. i	Input current distortion at rated input current	< 3%
5.2.2 k	AC power distribution system compatibility	TN-S, TN, TT and IT
	Backfeed protection	Yes, internal as standard

## ELECTRICAL CHARACTERISTICS

### OUTPUT

5.3.2 f	Number of output phases	3 phases + neutral
5.3.2 b	Rated output voltage	220/380 V; 230/400 V; 240/415 V, configurable
5.3.2 b	Output voltage variation, steady state	< +/-1.5%
5.3.2 i	Total voltage harmonic distortion 100% linear load 100% non-linear load	≤ 2% < 5%
5.3.2 q	Voltage unbalance at reference unbalanced load Phase displacement at reference unbalanced load	< +/-2,5% < +/-1,0°
5.3.2 c	Rated output frequency Slew rate	50 or 60 Hz, configurable 0,7 Hz/s
5.3.2 k	Rated output power	300 kVA/ 275 kW
5.3.2 l	Overload capability On inverter	10 min 110% load 30 sec 125% load 10 sec 150% load 300 ms >150% load
	Overload capability On bypass	Continuous < 115% load 20 ms 1000% load
5.3.2 m	Output current limitation, short-circuit capability	800 A, 300 ms L-N 760 A, 300 ms L-L
5.3.2 o and 5.3.2 p	Load power factor Rated Permitted range	0,9 0.7 lagging to 0.8 leading

# Eaton Power Xpert 9395P 300kVA/275kW UPS Technical Specification

Manufacturer's declaration in accordance with IEC 62040-3

IEC 62040-3 Subclause	<b>MODEL RATING (0,9 p.f.)</b>	<b>300kVA</b>
--------------------------	--------------------------------	---------------

## ESS MODE CHARACTERISTICS

	Transfer time to double-conversion Mains available Mains failure	No break Typically <2 ms
	Output voltage variation setting	±10% of nominal voltage, default
	Storm detection	UPS locks into double-conversion mode when three power line disturbances have forced the unit to double-conversion three times (user adjustable) within a one-hour period (user adjustable).
	High Alert mode	UPS will stay on double-conversion for one hour (user adjustable), after which the unit will automatically return to operate on ESS.

## BYPASS

	Type of bypass	Static
	Bypass rating	300 kVA
	Bypass voltage range	220/380 V; 230/400 V; 240/415 V tolerance -10% / +10% of 230V
	Transfer time break	No break
	Maintenance bypass	Available as an option
	Rated conditional short-circuit current, $I_{cc}$ Static Bypass Optional Integrated Maintenance	100 kA 50 kA* <i>*using external 630 A gG protective fuse</i>
	Internal static bypass ultra-rapid fuse	Bussmann 170M4467, 700A, 690Vac

## BATTERY CHARACTERISTICS

5.4.2.2 d	Battery technology	12 V, VRLA
5.4.2.2 b	Battery quantity	40 blocks, 240 cells per battery string
5.4.2.2 c	Battery voltage	480V (40 blocks)
5.4.2.2 o	Recharge profile	ABM or float
5.4.2.2 q	End of discharge voltage	1.67 VPC to 1.75 VPC Configurable or automatic (load adaptive)
5.4.2.2 r	Charging current limit	120 A

Author: Joel Kärkkäinen

Updated: 31.10.2017

Document: Power Xpert 9395P-300 technical specification\_Rev006

The technical specification is subject to change without notice.  
Page 4 of 5

# Eaton Power Xpert 9395P 300kVA/275kW UPS Technical Specification

Manufacturer's declaration in accordance with IEC 62040-3

IEC 62040-3 Subclause	<b>MODEL RATING (0,9 p.f.)</b>	<b>300kVA</b>
--------------------------	--------------------------------	---------------

## COMMUNICATION CIRCUITS

	Complete list of indications and interface devices	See User's Manual
--	--	-------------------

## COMPLIANCE WITH STANDARDS

IEC 62040-1	Safety Degree of protection	Access Operator access IP 20; protection against medium sized foreign matter (incl. finger)
IEC 62040-2	Electromagnetic Compatibility Immunity Emissions	EMC Category C3 EMC Category C3