



CABLE LENGTH SHOWN NOT TO SCALE




CIRCUIT SCHEMATIC



EBAB21 G3+ BASIC

FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
NONE	1Ø; 200-240V~; W+N+PE 50/60Hz 16A	(16) IEC 60320 C13 GRIP / P-LOCK	0 TO 60 ° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
LENGTH: 704MM WIDTH: 52 MM DEPTH: 53MM ALUMINIUM CHASSIS, BLACK MNT PATTERN SK-23919-Y1	IEC 60309 C20 16A 230V~ W+N+PE 1.5MM HO5 POWER CORD CABLE LENGTH: 3.0 M	200-240V~; 50/60Hz 10A PER C13 16A MAX TOTAL	CE, CB
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
NONE	NONE	STANDARD KSP026 - VERT INSTALLATION PACK KA35	EBA3CX8FABE72AM



PICTORIAL VIEW
SCALE 0.400

02 CHANGE PACK FROM KSP014 TO KSP026	24.06.2019	AEK	MB
01 REVISED ACCESSORIES IN SPECIFICATION TABLE.	12.06.2015	G.McD.	M.B.
00 INITIAL RELEASE	13.05.2014	RA	MB
REV / MODIFICATION	DATE	DESIGNER	VERIF.
		HEINEMANN PRODUCTS	VUE/VIEW 1ST ANGLE
		CH-1345 LE LIEU SWITZERLAND	ECHELLE / SCALE 4/10
TOLERANCE GENERALE / GENERAL TOLERANCE N/A		N/A	N° MAG EBAB21
TRAITEMENT / FINISH N/A		N/A	DESIGNE LE / DRAWED THE 13.05.2014
MATIERE / MATERIAL N/A		N/A	PAR / BY RA
NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT N/A		N/A	VERIFIE PAR / VERIFIED BY MB
DESIGNATION EPDU BA 0U (C20 16A 1P)16XC13		DIMENSIONS AND TOLERANCES IN MILLIMETERS	
COTES A CONTROLER INSPECTION DIMENSIONS		COTES FONCTIONNELLES FUNCTIONAL DIMENSIONS	NUMERO DU PLAN PLAN NUMBER
XX.XX		# XX.XX	02
<small>Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation. This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.</small>			