








REV	ECO No.	REVISION	DR	CK	AP	DATE
001	102474	ENGINEERING RELEASE	RS			09 MAY 16
002	106922	UP REV & ADDED EATON LOGO	LL			10 AUG 16
003	112005	REVISED SPK023 TO BE SPK014	RS			21 NOV 16
05	114096	ADDED UL, CE AND DENCO	RS			03 JAN 17
06	175225	PACKAGING REVISION	RS			01 NOV 19



REAR VIEW



EMA374-10 G3 MANAGED

FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT, POWER AND ENERGY METERING FOR INPUT, BRANCH AND OUTLET; OUTLET SWITCHING	IEC 60309 532P6W PLUG 10AWG / 5C & 5x6.0mm 10FT POWERCORD	(48) IEC 60320 C13 GRIP	UL 32° TO 140° F (0° TO 60° C) CE/DEMKO 32° TO 131° F (0° TO 55° C)
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
72" (1829mm) LENGTH 4.10" (104mm) WIDTH 2.10" (53mm) DEPTH ALUMINUM CHASSIS, BLACK	200-240 / 346-415V ~ 3W+N+PE 24A UL, 32A CE & DEMKO 50/60HZ	200-240V ~ 10A MAX PER C13 16A MAX PER SECTION 24A (UL), 32A (CE & DEMKO) MAX PER PHASE	  
BRANCHED CIRCUIT PROTECTION	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
(6) 20A 1-POLE LISTED 10KA INTERRUPTING CURRENT	NONE	INCLUDED SPK014 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE	EMA6DJ95TKD9BA1 SERIAL NUMBER B684 _____

METRIC	THIRD ANGLE PROJECTION	EATON CORPORATION, ELECTRICAL	EATON	SIZE D
DESCRIPTION: ePDU G3 SPECIFICATION DRAWING FOR EMA374-10				
MODIFIED BY: R.SIEGFRIED	DATE: 09 MAY 2016	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: ANGLES: ±1/2° DIMENSIONAL: 0.X: ±0.75 X, (FOR X < 3): ±1 HOLES: Ø<0.13 Ø<0.25 X (FOR X > 3): ±2.5 DIMENSIONS ARE IN MILLIMETERS (INCHES) AND AFTER PLATING		SCALE: 0.300 DO NOT SCALE DRAWING OR CHANGE MANUALLY
ECO: 102474	STATE: RELEASED	PRO-ENGINEER GENERATED	PART NAME: EMA6DJ95TKD9BA1	REVISION: 06 SHEET: 1 of 1
EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON, IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON CORPORATION AND IS SUBJECT TO RECALL BY EATON AT ANY TIME. BY TAKING POSSESSION OF THIS DOCUMENT, THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTERESTS OF EATON, AND THAT NO PORTION OF THIS DOCUMENT MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON. IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2008 Eaton Corporation - All Rights Reserved.				