

EPR48-3G Rectifier Module



The **Eaton® EPR48-3G Enterprise Power Rectifiers** are designed specifically for enterprise applications such as PoE and VoIP converged data networks, customer premises equipment and also tele-communications roadside cabinet installations.

The EPR48-3G is a telecom network grade rectifier with 900W output. It is designed for operation at up to 70°C (158°F) and under a wide range of AC power conditions.

The EPR48-3G rectifier is microprocessor controlled and includes intelligent features such as automatic set up during installation, temperature dependant variable speed fans for lowest audible noise and automatic self protection over wide ranging environmental conditions.

The EPR48-3G also has power factor correction and is up to 91% efficient, with optimum performance available at typical load currents. Together these give the EPR48-3G some of the lowest running costs for any DC power system of its type available.

The EPR48-3G rectifier module will provide years of costeffective, and trouble free service for your 48V enterprise access equipment.

Typical Applications:

- PoE equipment
- VoIP/IP converged data networks
- PABX for any business network
- Telecom roadside cabinets

Features

- Fast on-line expansion of rectifiers (hot-swap)
- Automatic set-up from system controller
- Intelligent microprocessor controlled
- High efficiency and unity power factor
- Universal AC supply input
- Wide output voltage ranges
- Constant power output
- Compliance with international standards



Powering Business Worldwide

Technical Specifications

Input

AC Supply	Nominal: 220/240V, 50/60Hz Extended Operating Range: 90V – 275V
Power Factor	>0.98 (50 – 100% Output Current)
Efficiency	91% (50 – 100% Output Current)

Output

DC Output Voltage Range	48V: 43 – 57.5V
DC Output (maximum)	900W (240V AC nominal) 550W (120V AC nominal)

Environmental

Operating Temperature Range	-40°C – +70°C [-40°F – +158°F] Output current is derated above 50°C [122°F]
Cooling	Temperature controlled, variable speed, high reliability fans

Mechanical

Dimensions H,W,D	3U: 133mm [5.25"], 42mm [1.65"], 266mm [10.45"] overall
Weight	1.7kg [3.7 lb]

Certifications

North America	UL, FCC Verification
Europe	CE
Australia / New Zealand	C-tick, Telepermit

In the interests of continual product improvement all specifications are subject to change without notice. Performance ratings are valid with all other variables at Nominal. Specifications guaranteed over rated operating range.

Email: dc.info@eaton.com
www.eaton.com/dcpowersolutions