

**EMAH06**



**General**

|              |                        |
|--------------|------------------------|
| Style Number | EMAH06                 |
| Part Number  | EMAH06                 |
| Availability | Usually in stock       |
| MIB          | available for download |

**Physical**

|                            |  |
|----------------------------|--|
| Dimensions (H x W x D, mm) | 445x225x87   |
| Mounting Style             | Button mounting on rear and sides, variable mounting bracket. 1U/2U form factor ePDUs can be mounted horizontally, vertically, or under a surface. |
| Form factor                | 2U   |

**Input**

|                  |                   |
|------------------|-------------------|
| Max kW           | 7                 |
| Plug             | (1) IEC 60309 32A |
|                  |                   |
| Cable Length (m) | 3                 |
| Voltage          | 230V              |
| Current          | 32                |
| Phase            | Single-phase      |
| Frequency        | 50Hz              |

**Output**

|                      |     |
|----------------------|-----|
| Grip cable retention | Yes |
| Outlets              |     |

(12) IEC-320-C13 (4) IEC-320-C19



|                  |               |
|------------------|---------------|
| Circuit Breakers | 2 single pole |
| Outlet Control   | Yes           |

### Protection & Filtering

|                         |      |
|-------------------------|------|
| Spike/Surge Suppression | None |
| EMI/RFI Filter          | None |

### Control & Interface

|   |  |
|---|--|
| Daisy Chain                             | 8 ePDUs  |
| Operating Temperature                   | 60 Degrees C   |
| Hot Swap Network and Control            | Yes  |
| Communication and Protocols             | HTTP, HTTPS, SSL, Telnet, FTP, SNMP, SMTP, DNS, DHCP, LDAP, RADIUS |
| Optional Temperature and Humidity probe | EMP001   |
| Environmental Interface                 | Yes  |
| Serial Interface                        | Yes  |
| Ethernet Interface                      | Yes  |
| Voltage Monitoring                      | Yes  |

### Metering and Switching

|                                   |  |
|-----------------------------------|--|
| Metering                          | Outlet and Equipment Monitoring across A and B feed        |
| Metering Characteristics          | V, W, A and kWhr, Active power, Apparent Power, Peak Power |
| Metering Accuracy                 | IEC Class 1 Billing grade Accuracy                         |
| Level 3 PUE measurements          | Yes  |
| Circuit breaker status monitoring | Yes  |
| Switching                         | Outlet and Equipment Switching across A and B feed         |

### Environmental & Approval Standards

|                               |  |
|-------------------------------|--|
| Approvals                     | CB, CE, EN 60950-1:2006/A11:2009/A1:2010/A12:2011 Safety - Part 1: General Requirements, IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1 EN 55022:2010 Radio Disturbance characteristics - Limits and methods of measurement. EN 55024:2010 Immunity characteristics - Limits and methods of measurement. |
| Electromagnetic compatibility | EN 61000-6-2:2005 Part 6-2: Generic standards - Immunity for industrial environments EN 61000-6-4:2007+A1:2011 Part 6-4: Generic standards - Emission standard for industrial environments   |
| Environmental                 | RoHS Directive – 2011/65/EU, EN 50581 : 2012, REACH Regulation   |

(CE No. 1907/2006), WEEE directive 2012/19/EU, PEP ecopassport (Basic ePDUs) Packaging: 100% recycled, 100% recyclable: no plastic, no metal, no foam.

Manufacturing Plant

ISO 9001:2008 / ISO 14001:2004

## Warranty

Standard warranty

2 years

[Privacy Policy](#)  
[Terms & Conditions](#)  
[Copyright](#)

© 2019 Eaton  
All Rights Reserved