





| LTR | ECO No. | REVISION | DR | CK | AF | AP | DATE |
|-----|---------|---|------|----|----|----|-----------|
| A | | ENGINEERING RELEASE | MDV | | | | 10/10/05 |
| B | 8548 | UPDATE CHASSIS & TEXT | LS | | DK | | 20 FEB 08 |
| C | 8593 | CORR OUTPUT CABLE LENGTH | LS | | DK | | 09 JUN 08 |
| D | 8793 | UPDATE BORDER, LOGO, TEXT, GND SCREW | J.O. | | | | 12 FEB 10 |
| E | 11470 | UPDATE EATON LOGOS | GS | | | | 18 MAY 10 |
| 002 | 064663 | ADD ROHS NOTES | HN | | | | 30 APR 14 |



NOTES

- RACK MOUNTED STEEL CHASSIS, BLACK MEDIUM TEXTURE
19.00" WIDE STANDARD RACK MOUNT WITH ADJUSTABLE BRACKETS
1.72" HIGH
7.00" DEEP
UNIT REQUIRES CHASSIS SUPPORT BRACKETS
- DUAL INPUT:
PRIMARY: 120 VAC 24A, SINGLE PHASE, 50/60HZ
CABLE: 9 FOOT 10/3 SJOOW CABLE WITH NEMA L5-30 PLUG
SECONDARY: 120 VAC 24A, SINGLE PHASE, 50/60HZ
CABLE: 9 FOOT 10/3 SJOOW CABLE WITH NEMA L5-30 PLUG
- OUTPUT: 120 VAC 24 AMPS AT NEMA L5-30 RECEPTACLE ON 6-INCH 10/3 SJOOW CABLE
- FILTER: NONE
- SPIKE SURGE PROTECTION: LINE TO NEUTRAL
- CIRCUIT BREAKER: ONE 1-POLE 30A, U.L. RECOGNIZED
- INDICATOR LIGHTS: FIVE
1 BLUE, ON WHEN THERE IS POWER TO OUTLETS
4 GREEN, DISPLAYS POWER AVAILABLE FROM DUAL SOURCE, AND IDENTIFIES THE SOURCE IN USE
- AUTOSWITCH BETWEEN PRIMARY AND SECONDARY POWER SOURCE

| INPUT VOLTAGE | DROP-OUT | PULL-IN |
|-----------------|----------|---------|
| 120 VAC SETTING | 90 | 103 |
- MINIMUM POWER FACTOR OF .85 LEADING OR LAGGING
- UL RECOGNIZED COMPONENTS WHERE APPLICABLE.
- RoHS COMPLIANT PER DIRECTIVE 2011/65/EU WITH APPLICABLE EXEMPTIONS.
- ALL MATERIALS AND SUB-MATERIALS COMPLY WITH EATON SPECIFICATION 164080496. DOCUMENTATION CERTIFYING COMPLIANCE TO EATON SPECIFICATION 164080496 IS AVAILABLE UPON REQUEST.



EATON APPROVAL DATE

EATON 9650 Jeronimo Road, Irvine, California 92618
Phone (949) 452-8500 www.ePDU.com

THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERETO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES

| | | | |
|-------------------------------------|----------------------------|---------------------|---------------------------------|
| DIMENSIONS IN INCHES TOLERANCES: | | TITLE | |
| DECIMALS | ANGLES | ENGINEERING DRAWING | |
| XX ±.000 | ± 0.5° | T2235-3369 | ASSY 3369 |
| XXX ±.010 | UNLESS OTHERWISE SPECIFIED | DRAWN BY: MDV | DWG FILENAME: T_2235_3369_MEDWG |
| SCALE | SIZE | SHEET | DWG NO. |