





LTR	ECO No.	REVISION	DR	CK	AP	AP	DATE
A	NONE	ENGINEERING RELEASE	MDV				02/17/03
B	8399	ADD RoHS NOTE & UL LISTING	J.O.				07 NOV 06
C	8548	UPDATE CHASSIS & TEXT	LS		DK		19 FEB 08
D	11941	UPDATE EATON LOGOS	GS				25 MAY 10
002	064861	ADD ROHS NOTES	HN				06 MAY 14



**NOTES:**

- RACK MOUNTED STEEL CHASSIS, BLACK MED. TEXTURE  
19.00" WIDE STD. RACK MOUNTING WITH ADJUSTABLE BRACKETS  
1.72" HIGH  
9.50" DEEP  
CHASSIS SUPPORT BRACKETS REQUIRED
- DUAL INPUT:  
PRIMARY: 200-240VAC 24A SINGLE PHASE, 50/60HZ  
9 FOOT 10/3 SOOW CABLE WITH L6-30P  
SECONDARY: 200-240VAC 24A SINGLE PHASE, 50/60HZ  
9 FOOT 10/3 SOOW CABLE WITH L6-30P  
VOLTAGE SELECTION SWITCH ON FRONT PANEL:
 

INPUT VOLTAGE	DROP-OUT	PULL-IN
120 VAC	90	103
208 VAC	182	195
240 VAC	197	210
- MINIMUM POWER FACTOR OF .85 LEADING OR LAGGING
- OUTPUT: 200-240 VAC, 24 AMPS MAX TOTAL  
SECTION 1: 6 IEC 60320 C-13 OUTLETS, 12 AMP MAX  
SECTION 2: 6 IEC 60320 C-13 OUTLETS, 12 AMP MAX
- FILTER: NONE
- SPIKE SURGE PROTECTION: LINE TO LINE
- CIRCUIT BREAKER: TWO 2-POLE 15 AMP UL LISTED BREAKERS
- INDICATOR LIGHTS: SIX  
2 BLUE, ONE PER SECTION, ON WHEN THERE IS POWER TO OUTLETS  
4 GREEN, DISPLAYS POWER AVAILABLE FROM DUAL SOURCE, AND IDENTIFIES THE SOURCE IN USE.
- U.L./cUL LISTED PRODUCT.
- RoHS COMPLIANT PER DIRECTIVE 2011/65/EU WITH APPLICABLE EXEMPTIONS.
- ALL MATERIALS AND SUB-MATERIALS COMPLY WITH EATON SPECIFICATION 164080496. DOCUMENTATION CERTIFYING COMPLIANCE TO EATON SPECIFICATION 164080496 IS AVAILABLE UPON REQUEST.



EATON APPROVAL \_\_\_\_\_ DATE \_\_\_\_\_

THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERETO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2009 EATON CORP

		9650 Jeronimo Road, Irvine, California 92618 Phone (949) 452-8500 www.epdu.com	
		TITLE ENGINEERING DRAWING T2235-F3-CNB09L ASSY 2895	
DIMENSIONS IN INCHES TOLERANCES: DECIMALS .XX ±0.05 .XXX ±0.01 .XXX OTHERWISE SPECIFIED CAGE CODE 51795	DRAWN BY: MDV SCALE: 1:1 SHEET: D SHEET NO.: 1 OF 1	DWG FILENAME: T_2235_F3_CNB09L_2895_ME.DWG DWG NO.: T_2235_F3_CNB09L_2895_ME	REV: 002