



| REV | DATE | ECO-CODE | MODIFICATION | PREPARED | APPROVED |
|-------------|------|----------|--------------|----------|----------|
| 18-AUG-2023 | | | FIRST ISSUE | | |



EVMAL630X G4 MANAGED

| | | | |
|---|---|--|------------------------------|
| FUNCTIONALITY | INPUT | OUTPUT | ENVIRONMENTAL |
| CURRENT, POWER, AND ENERGY METERING FOR INPUT AND OUTLET; CURRENT METERING FOR BRANCH; OUTLET SWITCHING | NEMA L6-30 10AWG / 3C 10FT POWERCORD | (24) IEC 60320 C13 (18) EATON C39 - COMBO C13/C19 | 0° TO 60° C 32° TO 140° F |
| MECHANICAL | INPUT RATING | OUTPUT RATING | CERTIFICATIONS |
| 68.11" (1730mm) LENGTH 2.05" (52mm) WIDTH 2.09" (53mm) DEPTH ALUMINUM CHASSIS, BLACK | 200-240V ~ 2W + PE 24A 50/60HZ | 200-240V ~ ; 10A PER C13, 16A PER C39 16A MAX PER SECTION 24A MAX PER PHASE | cTUVus |
| CIRCUIT BREAKERS | COMMUNICATION | ACCESSORIES | REGULATORY MODEL |
| (3) 20A 2-POLE LISTED | G4 eNMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY | INCLUDED SPK045 - INSTALLATION OPTIONAL USB-C TO RS232 ADAPTER - U209-006-RJ45XC OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 | EMAF-MTXJ-E27K |



| METRIC | | THIRD ANGLE PROJECTION | NAME (PART NUMBER) | REVISION | EATON |
|--|--|------------------------|----------------------|----------|---------|
| | | | 9001-22308_EVMAL630X | | |
| DESCRIPTION: PDU G4 MA 0U L6-30P 24xC13,18xC39 | | | | | SIZE: D |
| ORIGINATED BY: | SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING | STATE: | SCALE: 0.400 | | |
| MODIFIED BY: | INTERPRET DIM AND TOL PER ASME Y14.5-2018 | ECO: | SHEET: 1 OF 1 | | |
| <small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY. NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION: THIS DOCUMENT IS THE PROPERTY OF EATON CORPORATION AND IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE DRAWING AND IS NOT TO BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT THE WRITTEN PERMISSION OF EATON CORPORATION. ANY UNAUTHORIZED REPRODUCTION OR USE OF THIS DOCUMENT IS STRICTLY PROHIBITED. EATON CORPORATION SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING CONSEQUENTIAL DAMAGES, ARISING FROM THE USE OF THIS DOCUMENT. THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT © Eaton Corporation. All Rights Reserved.</small> | | | | | |