



EMA367-10
G3 MANAGED

| | | | |
|---|---|--|---|
| FUNCTIONALITY | INPUT | OUTPUT | OPERATING TEMPERATURE |
| CURRENT, POWER, AND ENERGY METERING FOR INPUT, BRANCH AND OUTLET; OUTLET SWITCHING | NEMA L21-20P 10FT 12AWG/5C POWERCORD | (1) NEMA 5-20R (21) IEC 60320 C13 GRIP (6) IEC 60320 C19 GRIP | 32° TO 140° F 0° TO 60° C |
| MECHANICAL | INPUT RATING | OUTPUT RATING | CERTIFICATIONS |
| 72.01" (1829mm) LENGTH 2.05" (52mm) WIDTH 2.56" (65mm) DEPTH ALUMINUM CHASSIS, BLACK | 120/208V~ WYE 3W+N+PE 16A 50/60 Hz | 120V~, 16A PER 5-20 200-240V~, 10A PER C13; 16A PER C19 16A MAX PER SECTION 16A MAX PER PHASE | |
| CIRCUIT BREAKERS | FILTER AND SPIKE/SURGE | ACCESSORIES | CONFIGURATION |
| (3) 20A 2-POLE LISTED | NONE | INCLUDED SPK012 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE | EMA6PB15JFC8BB1 SERIAL NUMBER B674 _____ |

| | | | |
|----------|-------------------------|-------------------|-----------------------|
| TITLE | ePDU G3 SPECIFICATION | DRAW | H. NGUYEN 27 JUL 2015 |
| DWG NO. | EMA6PB15JFC8BB1 REV 001 | DESIGN | |
| MATERIAL | | CHECKED | |
| COATING | | SAFETY | |
| UNITS | in[mm] | APPROVED | |
| SHEET | 1/1 | ELECTRICAL SECTOR | |