


<b>EVMAF132A</b>	<b>G4 Rack PDU MANAGED</b>		
<b>FUNCTIONALITY</b>	<b>INPUT</b>	<b>OUTPUT</b>	<b>ENVIRONMENTAL</b>
CURRENT, POWER, AND ENERGY METERING FOR INPUT, BRANCH AND OUTLET; OUTLET SWITCHING	IEC 60309-2 32A 230V~ 6.0MM^2 x 3C POWERCORD (LSZH) CABLE LENGTH: 3.0M	(12) IEC 60320 C13 HIGH RETENTION / P-LOCK (12) EATON C39 - COMBO C13/C19 HIGH RETENTION / P-LOCK (C19 ONLY)	OPERATING TEMPERATURE 0° TO 60° C 32° TO 140° F
<b>MECHANICAL</b>	<b>INPUT RATING</b>	<b>OUTPUT RATING</b>	<b>CERTIFICATIONS</b>
1730mm (68.11") LENGTH 52mm (2.05") WIDTH 53mm (2.09") DEPTH ALUMINUM CHASSIS, BLACK	200-240V~ W+N+PE 32A 50/60Hz	200-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 32A MAX TOTAL	CE, UKCA, RCM, Cmm, Ukr, EAC
<b>CIRCUIT BREAKERS</b>	<b>COMMUNICATION</b>	<b>ACCESSORIES</b>	<b>REGULATORY MODEL</b>
(2) 16A 1-POLE	G4 NMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY UL 2900-1 and IEC 62443-4-2	SPARE PART ACCESSORY KIT SPK050 OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 SPARE PART G4 NMC SPK055	EMAF-CHFB-C37K



03	GLOBAL UPDATE	26.10.2023	RP	YS
00	FIRST RELEASE	06.09.2023	RP	YS
REV.	MODIFICATION	DATE	DESS/DRAW	VERIF
		ECHELLE / SCALE	N° MAG	
		0.4	9001-22325	
		DESSINE LE / DRAWED THE	06.09.2023	
		PAR / BY	RP	
		VERIFIE PAR / VERIFIED BY	YS	
TOLERANCE GENERALE / GENERAL TOLERANCE		± 0.3	± 0°20'	
TRAITEMENT / FINISH		NA		
MATIERE / MATERIAL		NA		
NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT		X	DIMENSIONS AND TOLERANCES IN MILLIMETERS	
DESIGNATION		PDU G4 MA 0U 309 32A 1P 12xC13,12XC39	9001-22325_EVMAF132A	03
COTES A CONTROLER / INSPECTION DIMENSIONS		XX.X	NUMERO DU PLAN / PLAN NUMBER	
			DRAWING REV.	

Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation.  
This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.