



**EMACFB3XAE4J2_2
G3 HD MANAGED**

| | | | |
|--|--|--|---|
| FUNCTIONALITY | INPUT | OUTPUT | CERTIFICATIONS |
| CURRENT, POWER AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING | IEC 60309 516P6W PLUG 10FT 11AWG / 4mm ² , 5C POWERCORD END ENTRY | (39) IEC C13 GRIP (6) IEC C19 GRIP | UL/cUL LISTED CE |
| MECHANICAL | INPUT RATING | OUTPUT RATING | CONFIGURATION |
| 68.03" (1728mm) LENGTH 2.05" (52mm) WIDTH 2.24" (57mm) DEPTH ALUMINUM CHASSIS | 200-240 / 346-415V~ WYE, 3W+N+PE 16A 50/60Hz | 200-240V~ 10A PER C13, 16A PER C19 16A MAX PER SECTION 16A MAX PER PHASE | EMACFB3XAE4J2K2 - BLACK EMACFB3XAE4J2B2 - BLUE EMACFB3XAE4J2R2 - RED EMACFB3XAE4J2W2 - WHITE EMACFB3XAE4J2E2 - GREY EMACFB3XAE4J2N2 - BROWN EMACFB3XAE4J2A2 - ORANGE EMACFB3XAE4J2U2 - PURPLE EMACFB3XAE4J2G2 - GREEN EMACFB3XAE4J2P2 - PINK EMACFB3XAE4J2Y2 - YELLOW |
| CIRCUIT BREAKERS | ENVIRONMENTAL | ACCESSORIES | |
| NONE | 32° TO 140°F 0° TO 60°C | INCLUDED SPK033 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE | |

| | | | | |
|--|----------------------------|---|--------------|---|
| METRIC | THIRD ANGLE PROJECTION | EATON CORPORATION, ELECTRICAL | EATON | SIZE D |
| DESCRIPTION: ePDU G3HD SPECIFICATION FOR EMACFB3XAE4J2_2 | | | | |
| MODIFIED BY: E0081951 | DATE: 22 JAN 20 | UNLESS OTHERWISE SPECIFIED TOLERANCES ON DIMENSIONS ARE: ANGLES: ±1/2° DECIMALS: 0.X: ±0.25 X, (FOR X < 3): ±1 HOLES: ⌀±0.13 0.XX: ±0.25 X, (FOR X > 3): ±2.5 | | SCALE: 0.300 DO NOT SCALE DRAWING OR CHANGE MANUALLY |
| ECD: ECD-172188 | STATE: GENERATED | DIMENSIONS ARE IN MILLIMETERS (INCHES) AND AFTER PLATING | | SHEET: 1 of 1 |
| PRO-ENGINEER GENERATED | PART NAME: EMACFB3XAE4J2_2 | REVISION: 05 | | |
| <small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON, IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON CORPORATION, AND IS HEREBY ON LOAN AND SUBJECT TO RECALL BY EATON AT ANY TIME. BY TAKING POSSESSION OF THIS DOCUMENT, THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTERESTS OF EATON, AND THAT NO PORTION OF THIS DOCUMENT MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON. IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2008 Eaton Corporation - All Rights Reserved.</small> | | | | |