





LTR	ECO No.	REVISION	DR	CR	AP	AP	DATE
A		ENGINEERING RELEASE	MBP				10/19/00
B	6379	REMOVE VARISTOR SWITCH	J.O.				6 JULY 01
C	7506	CORRECT SILKSCRN, NOTES	MDV				05/02/03
D	7910	REMOVE AGENCY LABEL	LS		DK		28 MAY 04
E	014333	UPDATE BORDER & SCREEN	JF				23 AUG 10



**DANGER HIGH VOLTAGE**  
**DO NOT REMOVE COVER BEFORE DISCONNECTING POWER CABLE**

1. RACK MOUNT STEEL CHASSIS, GOLD ZINC PLATED  
 19.00" WIDE, WITH STANDARD RACK MOUNT BRACKETS  
 3.36" HIGH (2U)  
 13.00" DEEP  
**NOTE: CHASSIS SUPPORT BRACKETS OR SLIDES ARE REQUIRED**
2. INPUT: 120/208 VAC 24A, 3 PHASE WYE 50/60 Hz  
 CABLE: 15 FEET 10/5 SOOW, WITH L21-30 PLUG
3. OUTPUT:  
 FOUR 5-15 AND TWO L5-15 OUTLETS PER PHASE  
 PHASE X: J1-J6, BACK PANEL, 24 AMPS  
 PHASE Y: J7-J12, BACK PANEL, 24 AMPS  
 PHASE Z: J13-J16, BACK PANEL, 16 AMPS  
 PHASE Z: J17-J18, FRONT PANEL, 8 AMPS  
 24 AMPS MAX PER PHASE
4. CIRCUIT BREAKERS (UL LISTED):  
 ONE MAIN 3-POLE 30 AMP BREAKER  
 THREE 2-POLE 15 AMP BREAKERS, ONE PER PHASE
5. INDICATOR LIGHTS (4 GREEN):  
 ONE FOR MAIN BREAKER;  
 ONE FOR EACH PHASE
6. FILTER: EMI/RFI FILTER, 30 AMP 3 PHASE  
 COMMON MODE, LINE TO GROUND  
 DIFFERENTIAL MODE, LINE TO LINE
7. SPIKE/SURGE PROTECTION: NONE
8. UL/cUL LISTED PRODUCT



EATON APPROVAL

THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERETO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2010 EATON CORP

		8850 Jeronimo Road, Irvine, California 92618 Phone (949) 452-9500 www.epdu.com	
DIMENSIONS IN INCHES TOLERANCES: DECIMALS ANGLES .XX ±0.5° ±.020 UNLESS OTHERWISE SPECIFIED .XXX ±0.10 CAGE CODE 31785		TITLE ENGINEERING DRAWING FOR PC2646 ASSY 2686	
DRAWN BY: MDV SCALE: 1:1 SHEET: D OF 1	DWG FILENAME: PC_2646_2686_ME.DWG SHEET NO.: PC_2646_2686_ME	REV E	