



REVISIONS				
REV.	ECN #	DESCRIPTION	DATE	APPROVED
X0		SUBMITTAL RELEASE	10/25/19	AD

CONDUIT AREA




TOP VIEW



**FRONT VIEW
NO DOORS**

3 FUSE PANEL BEHIND DOOR



FRONT VIEW

3 PDG2-FRAME CB 12X225A OUTPUT

3 DISPLAY: -WAVESTAR HMI COLOR

3 CONTROL CHASSIS: -M4G -CONTRACTOR BOARD ENHANCED -BCMS

3 MAIN INPUT

5

36.00

4

6.00


200% NEUTRAL BUSBAR (RH & LH)

48.00

**SIDE VIEW
PANELS REMOVED**

CONDUIT AREA

4X Ø.63 MTG HOLES



BOTTOM VIEW

- 7 RECOMMENDED INPUT CABLE SIZE: (3) 300MCM CU PER PHASE
- 6 APPROXIMATE WEIGHT: 6500 LBS
- 5 MINIMUM CLEARANCE FOR DOORS.
- 4 MINIMUM VENTILATION CLEARANCE FOR REAR AND ONE SIDE OF UNIT.
- 3 ALL OPERATOR CONTROLS ARE FRONT ACCESS WITHOUT EXPOSURE TO LIVE PARTS.
- 2 ALL ROUTINE MAINTENANCE IS FRONT AND SIDE ACCESS.
- 1 DIMENSIONS IN [] ARE MILLIMETER.

NOTES: UNLESS OTHERWISE SPECIFIED:

		THIRD ANGLE PROJECTION			THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED WRITTEN PERMISSION OF POWER DISTRIBUTION, INC.	
MATERIAL: N/A		APPROVALS		DESCRIPTION: PDU 625KVA 1X900A 12X225A		
APPROVALS		DATE		SIZE B	DWG. NO. 11300118SUB	
DRAWN BY AD	10/25/2019	CHECKED BY KN	10/25/2019	REV X0		
APPROVED BY MW	10/25/2019	SCALE:		SHEET 1 OF 1		