



GENERAL SPECIFIED

CABINET CHARACTERISTIC:
ENCLOSURE : NEMA 1
LOCATION : INDOOR

MECHANICAL:
MOUNTING: BOLT DOWN ON CONCRETE OR FLOOR STAND
MATERIAL: STEEL
WEIGHT : 3500 LBS. APPROX.

ELECTRICAL:
INPUT #1: 480 VAC 3PH-4W W/GND @ 60 HZ, 250A MAX.
OUTPUT SUBFEEDS #1-8: 120/208 VAC, 100% CONTINUOUS LOAD (400 A MAX)
(2 EA. # 2/O-500 MCM AL/CU)

ENVIROMENTAL:
OPERATING AMBIENT TEMPERATURE 0°C TO 40°C (32° F TO 104°F)
RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING
ALTITUDE: 10,000 FT MAX

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
[] IN MILLIMETER
ANGULAR: ±0.5° BEND ±1°
TWO PLACE DECIMAL ±0.02
THREE PLACE DECIMAL ±0.005

THIS DRAWING CONTAINS
CONFIDENTIAL & PROPRIETARY
INFORMATION AND SHALL NOT
BE DISCLOSED OR COPIED
WITHOUT THE EXPRESSED,
WRITTEN PERMISSION OF
SMITHS POWER



THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING	
APPROVALS		DATE	
DRAWN	RAE	3/28/17	
CHECKED	WB	3/28/17	
ENG. APPR.			

TITLE: PP2 OUTLINE 150 KVA, (8) 400A SUBFEEDS		
SIZE B	DWG. NO. PDU56864	REV A
PART NO.		SHEET 1 OF 1