



EVMIF116A	G4 Rack PDU METERED INPUT		
FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT POWER AND ENERGY METERING FOR INPUT AND BRANCH	IEC 60309-2 16A 230/400V 2.5MM ² x 3C POWERCORD (LSZH) CABLE LENGTH: 3.0 M	(12) IEC 60320 C13 HIGH RETENTION / P-LOCK (12) EATON C39 - COMBO C13/C19 HIGH RETENTION / P-LOCK (C19 ONLY)	0° TO 60° C 32° TO 140° F
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
1000mm (39.37") LENGTH 52mm (2.05") WIDTH 53mm (2.09") DEPTH ALUMINUM CHASSIS, BLACK	200-240 / 346-415V~ WYE, 3W+N+PE 16A 50/60Hz	200-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION NOT TO EXCEED INPUT RATING	CE, UKCA, RCM, Cmim, Ukr, EAC
CIRCUIT BREAKERS	COMMUNICATION	ACCESSORIES	REGULATORY MODEL
NONE	G4 NMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY UL 2900-1 and IEC 62443-4-2	SPARE PART ACCESSORY KIT SPK050 OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 OPTIONAL G4 NMC - SPK055	EMIF-CEFA-A31K

02	GLOBAL UPDATE	26.10.2023	RP	YS
00	FIRST RELEASE	09.10.2023	RP	YS
REV.	MODIFICATION	DATE	DESSIN/DRAW	VERIF
EATON		HEINEMANN PRODUCTS	ECHELLE / SCALE	N° MAG
		CH-1345 LE LIEU SWITZERLAND	1/2	9001-22336
TRAITEMENT / FINISH NA		DESSINE LE / DRAWED THE	09.10.2023	
MATIERE / MATERIAL NA		PAR / BY	RP	
TOLERANCE GENERALE / GENERAL TOLERANCE ± 0.3 ± 0'20"		VERIFIE PAR / VERIFIED BY	YS	
NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT X		DIMENSIONS AND TOLERANCES IN MILLIMETERS		
DESIGNATION PDU G4 MI 0U 309 16A 1P 12xC13.12xC39		9001-22336_EVMIF116A	02	
COTES A CONTROLER / INSPECTION DIMENSIONS XX.X	COTES FONCTIONNELLES / FUNCTIONAL DIMENSIONS XX.X	NUMERO DU PLAN / PLAN NUMBER	DRAWING REV.	
Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation. This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.				