


8 7 6 5 4 3 2 1

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED



D  
C  
B  
A

D  
C  
B  
A



2 X 225A 42 P  
PANEL BOARD  
W SECONDARY  
BREAKER

(8) 225A SF



**GENERAL SPECIFIED**

FRONT ACCESS INSTALLATION AND MAINTENANCES  
 ALL OPERATORS CONTROL ISOLATED FROM HIGH VOLTAGE  
 MINIMUM 6 " CLEARANCE FOR SIDE AND REAR FOR VENTILATION  
 ELECTRICAL:  
 INPUT : 408 VAC 3PH-3W W/GND @ 60 HZ, 500MCM MAX  
 OUTPUT : 208 VAC 3PH-4W W/GND ( SEE ONE LINE FOR MORE DETAIL)

UNLESS OTHERWISE SPECIFIED:  
 DIMENSIONS ARE IN INCHES  
 [ ] IN MILLIMETER  
 ANGULAR: ±0.5° BEND ±1°  
 TWO PLACE DECIMAL ±0.02  
 THREE PLACE DECIMAL ±0.005

THIS DRAWING CONTAINS  
 CONFIDENTIAL & PROPRIETARY  
 INFORMATION AND SHALL NOT  
 BE DISCLOSED OR COPIED  
 WITHOUT THE EXPRESSED,  
 WRITTEN PERMISSION OF  
 SMITHS POWER



THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING	
APPROVALS		DATE	
DRAWN	IS	4/21/16	
CHECKED			
ENG. APPR.			

TITLE: OUTLINE POWPACK II 300 KVA, (2) 42P PNL BOARD, (8) 225A SF		
SIZE <b>B</b>	DWG. NO. <b>PDU20065</b>	REV
PART NO.		SHEET 1 OF 2

8 7 6 5 4 3 2 1