



<b>EVMAF116A</b>	<b>G4 Rack PDU MANAGED</b>		
<b>FUNCTIONALITY</b>	<b>INPUT</b>	<b>OUTPUT</b>	<b>ENVIRONMENTAL</b>
CURRENT, POWER, AND ENERGY METERING FOR INPUT, BRANCH AND OUTLET; OUTLET SWITCHING	IEC 60309-2 16A 230/400V 2.5MM <sup>2</sup> x 3C POWERCORD (LSZH) CABLE LENGTH: 3.0 M	(12) IEC 60320 C13 HIGH RETENTION / P-LOCK (12) EATON C39 - COMBO C13/C19 HIGH RETENTION / P-LOCK (C19 ONLY)	0° TO 60° C 32° TO 140° F
<b>MECHANICAL</b>	<b>INPUT RATING</b>	<b>OUTPUT RATING</b>	<b>CERTIFICATIONS</b>
1000mm (39.37") LENGTH 52mm (2.05") WIDTH 53mm (2.09") DEPTH ALUMINUM CHASSIS, BLACK	200-240 / 346-415V~ WYE, 3W+N+PE 16A 50/60Hz	200-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION NOT TO EXCEED INPUT RATING	CE, UKCA, RCM, Cmim, Ukr, EAC
<b>CIRCUIT BREAKERS</b>	<b>COMMUNICATION</b>	<b>ACCESSORIES</b>	<b>REGULATORY MODEL</b>
NONE	G4 NMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY UL 2900-1 and IEC 62443-4-2	SPARE PART ACCESSORY KIT SPK050 OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 SPARE PART G4 NMC SPK055	EMAF-CEFA-A31K

GLOBAL UPDATE		26.10.2023	RP	YS
FIRST RELEASE		08.09.2023	RP	YS
REV.	MODIFICATION	DATE	DESSIN/DRAW	VERIF
EATON		HEINEMANN PRODUCTS	ECHELLE / SCALE	N° MAG
CH-1345 LE LIEU SWITZERLAND		1/2	9001-22337	
TRAITEMENT / FINISH		NA	DESSINE LE / DRAWED THE	08.09.2023
MATIERE / MATERIAL		NA	PAR / BY	RP
TOLERANCE GENERALE / GENERAL TOLERANCE		± 0.3	± 0'20"	VERIFIE PAR / VERIFIED BY
NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT		X	DIMENSIONS AND TOLERANCES IN MILLIMETERS	
DESIGNATION		PDU G4 MA 0U 309 16A 1P 12xC13,12XC39	9001-22337_EVMAF116A	02
COTES A CONTROLER / INSPECTION DIMENSIONS		XX.X	NUMERO DU PLAN / PLAN NUMBER	
COTES FONCTIONNELLES / FUNCTIONAL DIMENSIONS		XX.X	DRAWING REV.	

Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation.  
This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.