


EVMIF132X	G4 Rack PDU METERED INPUT		
FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT POWER AND ENERGY METERING FOR INPUT AND BRANCH	IEC 60309-2 32A 230V~ 6.0MM ² x 3C POWERCORD (LSZH) CABLE LENGTH: 3.0M	(24) IEC 60320 C13 HIGH RETENTION / P-LOCK (18) EATON C39 - COMBO C13/C19 HIGH RETENTION / P-LOCK (C19 ONLY)	OPERATING TEMPERATURE 0° TO 60° C 32° TO 140° F
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
1730mm (68.11") LENGTH 52mm (2.05") WIDTH 53mm (2.09") DEPTH ALUMINUM CHASSIS, BLACK	200-240V~ W+N+PE 32A 50/60Hz	200-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 32A MAX TOTAL	CE, UKCA, RCM, Cmim, Ukr, EAC
CIRCUIT BREAKERS	COMMUNICATION	ACCESSORIES	REGULATORY MODEL
(2) 16A 1-POLE	G4 NMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY UL 2900-1 and IEC 62443-4-2	SPARE PART ACCESSORY KIT SPK050 OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 OPTIONAL G4 NMC - SPK055	EMIF-CHFB-C27K



01 GLOBAL UPDATE	26.10.2023	RP	YS
00 FIRST RELEASE	05.10.2023	RP	YS
REV. MODIFICATION	DATE	DESSIN/DRAW	VERIF
EATON		HEINEMANN PRODUCTS	ECHELLE / SCALE 0.4
CH-1345 LE LIEU SWITZERLAND		DESSINE LE / DRAWN THE PAR / BY RP	N° MAG 9001-22348
TRAITEMENT / FINISH NA		TOLERANCE GENERALE / GENERAL TOLERANCE ± 0.3 ± 0°20'	VERIFIE PAR / VERIFIED BY YS
MATIERE / MATERIAL NA		NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT X DIMENSIONS AND TOLERANCES IN MILLIMETERS	
DESIGNATION PDU G4 MI 0U 309 32A 1P 24xC13,18xC39	9001-22348_EVMIF132X	NUMERO DU PLAN PLAN NUMBER	01
COTES A CONTROLER INSPECTION DIMENSIONS XX.X	COTES FONCTIONNELLES FUNCTIONAL DIMENSIONS XX.X	Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation. This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.	