



NOTES:

1. OPERATOR INTERFACE PANEL.
2. MAIN INPUT CIRCUIT BREAKER.
3. 225A SECONDARY MAIN CIRCUIT BREAKER.
4. (42) POLE DISTRIBUTION PANELBOARDS.
5. CT STRIP FOR BCMS (OPTIONAL).
6. RECOMMEND A MINIMUM OF 36" IN REAR OR SIDE OF UNIT FOR MAINTENANCE.
7. MINIMUM OF 36" CLEARANCE FOR DOOR SWING.
8. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.
9. BCMS CIRCUIT BOARD (OPTIONAL).




OUTPUT CABLE AREA IN BOTTOM ONLY

FRONT VIEW (DOOR AND COVERS REMOVED)

REAR VIEW (DOOR AND COVERS REMOVED)

<p>THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.</p>	TITLE		-OUTLINE-	
	PDU (30-150 kVA) W/ LH FS SIDECAR		(6) 42 POLE PANEL BOARDS	
	DWG. NUMBER	SHEET 1 OF 1	REVISION	
	PDU19292		-A-	
DRAWN BY	RAE	CHECKED BY	MP	
DATE	10-28-15	DATE	10-28-15	



creating the perfect wave