


EVSWF132A	G4 Rack PDU SWITCHED		
FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT POWER AND ENERGY METERING FOR INPUT AND BRANCH; INDIVIDUAL OUTLET CONTROL	IEC 60309-2 32A 230V~ 6.0MM^2 x 3C POWERCORD (LSZH) CABLE LENGTH: 3.0M	(12) IEC 60320 C13 HIGH RETENTION / P-LOCK (12) EATON C39 - COMBO C13/C19 HIGH RETENTION / P-LOCK (C19 ONLY)	OPERATING TEMPERATURE 0° TO 60° C 32° TO 140° F
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
1730mm (68.11") LENGTH 52mm (2.05") WIDTH 53mm (2.09") DEPTH ALUMINUM CHASSIS, BLACK	200-240V~ W+N+PE 32A 50/60Hz	200-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION 32A MAX TOTAL	CE, UKCA, RCM, Cmm, Ukr, EAC
CIRCUIT BREAKERS	COMMUNICATION	ACCESSORIES	REGULATORY MODEL
(2) 16A 1-POLE	G4 NMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY UL 2900-1 and IEC 62443-4-2	SPARE PART ACCESSORY KIT SPK050 OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2 SPARE PART G4 NMC SPK055	ESWF-CHFB-C37K



01 GLOBAL UPDATE	26.10.2023	RP	YS
00 FIRST RELEASE	18.10.2023	RP	YS
REV. MODIFICATION	DATE	DESSIN/DRAW	VERIF
EATON		HEINEMANN PRODUCTS	ECHELLE / SCALE 0.4
CH-1345 LE LIEU SWITZERLAND		DESSINE LE / DRAWN THE RP	N° MAG 9001-22355
TRAITEMENT / FINISH NA		VERIFIE PAR / VERIFIED BY YS	
MATIERE / MATERIAL NA			
NIVEAU DU CERTIFICAT DE SOUMISSION REQUIS / SAMPLES APPROVAL PROCESS REPORT X		DIMENSIONS AND TOLERANCES IN MILLIMETERS	
DESIGNATION PDU G4 SW 0U 309 32A 1P 12xC13,12xC39	9001-22355_EVSWF132A	01	
COTES A CONTROLER INSPECTION DIMENSIONS XX.X	COTES FONCTIONNELLES FUNCTIONAL DIMENSIONS XX.X	NUMERO DU PLAN PLAN NUMBER	DRAWING REV.

Ce document est propriété de Eaton Industries Manufacturing GmbH. Duplication interdite sans autorisation.
This document is Eaton Industries Manufacturing GmbH property. Duplication forbidden without authorization.