

GENERAL SPECIFIED
CABINET CHARACTERISTIC: DOOR AND PANELS REMOVED
 ENCLOSURE : NEMA 1
 LOCATION : INDOOR

MECHANICAL:
 MATERIAL: STEEL
 FINISH: EXTERIOR PANELS: PEARL WHITE - PHTI-60016
 WEIGHT : 600 LBS. APPROX.



ELECTRICAL:
 INPUT #1: 208 VAC 3PH-4W W/GND @ 60 HZ, 225A (MAX) (2 EA. # 2/O-350 MCM CU)
 INPUT #2: 208 VAC 3PH-4W W/GND @ 60 HZ, 225A (MAX) (2 EA. # 2/O-350 MCM CU)
 OUTPUT PB #1: 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)
 OUTPUT PB #2: 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)

ENVIROMENTAL:
 OPERATING AMBIENT TEMPERATURE 0 °C TO 40 °C (32 ° F TO 104 °F)
 RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING
 ALTITUDE: 10,000 FT MAX

FRONT VIEW
DOOR AND PANELS REMOVED

SIDE VIEW
PANEL REMOVED

REAR VIEW
PANEL REMOVED

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: ANGULAR: ±0.5° BEND ±1° TWO PLACE DECIMAL ±0.02 THREE PLACE DECIMAL ±0.005		THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION, INC.		 PDI	
USED ON		DO NOT SCALE DRAWING			
MATERIAL: NA		APPROVALS		DATE	SIZE B DWG. NO. RPP18554 REV A
FINISH: NA		DRAWN ISF		5/19/15	
WEIGHT:		CHECKED LJN		5/19/15	
		ENG. APPR.			SCALE: 1:24
				PART NO.	SHEET 1 OF 1