

8 7 6 5 4 3 2 1

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
B	DRAWING UPDATED TO INCLUDE MOVE INPUT 2	2/9/2016	

D

C

B

A



D

C


B

A


MONITOR DISPLAY



SIDE PANELS REMOVE



BACK VIEW



GENERAL SPECIFIED

CABINET CHARACTERISTIC:

ENCLOSURE : NEMA 1
 LOCATION : INDOOR
 FINISH : EXTERIOR PANELS: PEARL WHITE - PHTI-60016
 WEIGHT : 375 LBS. APPROX.

ELECTRICAL:

INPUT1 : 208-120 VAC 3PH-4W W/GND @ 60 HZ, 400A (MAX) (2 EA. # 2/0-350 MCM CU)
 INPUT2:208-120 VAC 3PH-4W W/GND @ 60 HZ, 400A (MAX) (2 EA. #2/0-350 MCM CU)
 OUPUT:(2) 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)
 SEE PAGE 2 FOR ONELINE DIAGRAM
 OPERATING AMBIENT TEMPERATURE 0 °C TO 40 °C (32 ° F TO 104 ° F)
 RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING
 ALTITUDE: 10,000 FT MAX

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN INCHES
 () IN MILLIMETER
 ANGULAR: ±0.5° BEND ±1°
 TWO PLACE DECIMAL ±0.02
 THREE PLACE DECIMAL ±0.005

THIS DRAWING CONTAINS
 CONFIDENTIAL & PROPRIETARY
 INFORMATION AND SHALL NOT
 BE DISCLOSED OR COPIED
 WITHOUT THE EXPRESSED,
 WRITTEN PERMISSION OF
 SMITHS POWER



DO NOT SCALE DRAWING	
APPROVALS	DATE
DRAWN	
CHECKED	
ENG. APPR.	

TITLE: RPP - (2) MCCBS, (2) PANEL BOARDS		
SIZE B	DWG. NO. rpp19342	REV B
PART NO.		SHEET 1 OF 1

8 7 6 5 4 3 2 1