

VIEWS SHOWN WITHOUT DOORS AND BOTTOM ENTRY AND EXIT CONFIGURATION


LOGIC MODULE SWING OUT FOR TOP ENTRY INSTALLATION

TOUCH SCREEN DISPLAY

TRANSPARENT DOORS

BOTTOM REMOVABLE TRAY WITH DOUBLE 1/2" AND 3/4" CONDUIT KNOCK-OUT

REMOVABLE BOTTOM BLANK INPUT TRAY



SECTION A-A

GENERAL SPECIFIED

CABINET CHARACTERISTIC:  
ENCLOSURE : NEMA 1  
LOCATION : INDOOR

MECHANICAL:  
MOUNTING: BOLT TO CONCRETE FLOOR OR FLOOR STAND  
MATERIAL: STEEL  
WEIGHT : 3500 LBS. APPROX.

ELECTRICAL:  
INPUT #1: 208 VAC 3PH-4W W/GND @ 60 HZ, RANGE FROM 150A - 1200A (MAX)  
OUTPUT PB #1-#4: 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)  
OUTPUT SUBFEED #1-#4: 3-POLE, 600VAC MAX., 225A

FRONT ACCESS FOR INSTALLATION AND MAINTENANCE  
ALL OPERATOR CONTROL ARE FRONT ACCESS WITHOUT EXPOSE TO LIVE PARTS  
MINIMUM 6" FOR SIDE AND REAR FOR VENTILATION

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
[ ] IN MILLIMETER  
ANGULAR: ±0.5° BEND ±1°  
TWO PLACE DECIMAL ±0.02  
THREE PLACE DECIMAL ±0.005

THIS DRAWING CONTAINS  
CONFIDENTIAL & PROPRIETARY  
INFORMATION AND SHALL NOT  
BE DISCLOSED OR COPIED  
WITHOUT THE EXPRESSED,  
WRITTEN PERMISSION OF  
SMITHS POWER



|                        |     |                      |  |
|------------------------|-----|----------------------|--|
| THIRD ANGLE PROJECTION |     | DO NOT SCALE DRAWING |  |
| APPROVALS              |     | DATE                 |  |
| DRAWN                  | ISF | 12/14/16             |  |
| CHECKED                |     |                      |  |
| ENG. APPR.             |     |                      |  |

|  |                             |                 |
|--|-----------------------------|-----------------|
| TITLE:<br>PP2 SUBMITTAL DRAWING<br>300 KVA<br>(4) 225A SUBFEED, (4) PANEL BOAR |                             |                 |
| SIZE<br><b>B</b>   | DWG. NO.<br><b>PDU56438</b> | REV<br><b>A</b> |
| PART NO.   |                             | SHEET 1 OF 1    |