

Hot dip galvanized products

Three-piece couplings, clampbacks & clamps

THREE-PIECE CONDUIT COUPLINGS – HOT DIP GALVANIZED MALLEABLE IRON

Applications:

- Used to join two lengths of threaded conduit; couples conduit when conduit cannot be turned

Standard material:


- Malleable iron

Standard finish:

- Hot dip galvanized

Malleable iron (concrete tight)

UL File No. E-19189



Cat. #	Size	Unit qty.	Wt. lbs. per 100
190M HDG	1/2"	25	23
191 HDG	3/4"	25	35
192 HDG	1"	10	60
193 HDG	1 1/4"	5	91
194 HDG	1 1/2"	5	167
195 HDG	2"	5	215
196 HDG	2 1/2"	2	430
197 HDG	3"	1	463
198 HDG	3 1/2"	1	655
199 HDG	4"	1	800
188 HDG [ⓐ]	5"	1	1200
189 HDG [ⓐ]	6"	1	2100

[ⓐ]Not UL Listed.

CLAMPBACKS/SPACERS – HOT DIP GALVANIZED IRON

Applications:

- To provide space between conduit and mounting surface

UL File No. E-184283



Cat. #	Size	Unit qty.	Wt. lbs. per 100
CB1 HDG	1/2"	25	8
CB2 HDG	3/4"	25	10
CB3 HDG	1"	25	12
CB4 HDG	1 1/4"	25	21
CB5 HDG	1 1/2"	25	42
CB6 HDG	2"	10	40
CB7 HDG	2 1/2"	10	49
CB8 HDG	3"	10	62
CB9 HDG	3 1/2"	10	91
CB10 HDG	4"	10	110
CB11 HDG [ⓐ]	5"	5	135
CB12 HDG [ⓐ]	6"	5	225

[ⓐ]Not UL Listed.

CLAMPS – HOT DIP GALVANIZED IRON

Applications:

- To support rigid conduit and IMC to mounting surface

UL File No. E-184283



Cat. #	Size	Unit qty.	Wt. lbs. per 100
510 HDG	1/2"	100	6
511 HDG	3/4"	50	8
512 HDG	1"	50	13
513 HDG	1 1/4"	25	20
514 HDG	1 1/2"	20	30
515 HDG	2"	10	64
516 HDG [ⓐ]	2 1/2"	5	104
517 HDG [ⓐ]	3"	2	120
518 HDG [ⓐ]	3 1/2"	2	150
519 HDG [ⓐ]	4"	2	220
520 HDG [ⓐ]	5"	1	380
521 HDG [ⓐ]	6"	1	690

[ⓐ]Not UL Listed.

[ⓐ]Also for use with thin wall (EMT) conduit.

CONDUIT CLAMPS – RIGHT ANGLE TYPE – HOT DIP GALVANIZED IRON

Applications:

- Right angle – to attach the conduit run at a 90° angle to a beam or structural member
- Parallel type – to attach the conduit run parallel to a beam or structural member



Cat. #	Size	Load Rating Lbs.	Wt. lbs. per 100
RAC50HD	1/2"	30	37
RAC75HD	3/4"	50	40
RAC100HD	1"	60	42
RAC125HD	1 1/4"	75	49
RAC150HD	1 1/2"	80	54
RAC200HD	2"	100	71
RAC250HD	2 1/2"	125	95
RAC300HD	3"	165	107
RAC350HD	3 1/2"	200	120
RAC400HD	4"	330	131

Hot dip galvanized