



**GENERAL SPECIFIED**

CABINET CHARACTERISTIC:  
ENCLOSURE : NEMA 1  
LOCATION : INDOOR

MECHANICAL:  
MOUNTING: BOLT TO CONCRETE FLOOR OR FLOOR STAND  
MATERIAL: STEEL  
WEIGHT : 3000 LBS. APPROX.

ELECTRICAL:  
INPUT #1: 600 VAC MAX 3PH W/GND @ 60 HZ, 500A (MAX) (2 EA. 500 MCM COMPRESSION LUG)  
OUTPUT SUBFEED #1 - #6: 3-POLE, 600VAC MAX, 225A, 80% CONTINUOUS LOAD (3/0 - 350 MCM)

ENVIROMENTAL:  
OPERATING AMBIENT TEMPERATURE 0 °C TO 40 °C (32 ° F TO 104 °F)  
RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING  
ALTITUDE: 10,000 FT MAX

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
[ ] IN MILLIMETER  
ANGULAR: ±0.5° BEND ±1°  
TWO PLACE DECIMAL ±0.02  
THREE PLACE DECIMAL ±0.005

THIS DRAWING CONTAINS  
CONFIDENTIAL & PROPRIETARY  
INFORMATION AND SHALL NOT  
BE DISCLOSED OR COPIED  
WITHOUT THE EXPRESSED,  
WRITTEN PERMISSION OF  
SMITHS POWER



THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING	
APPROVALS		DATE	
DRAWN	ISF	2/2/2017	
CHECKED			
ENG. APPR.			

TITLE: <b>(6) 225A SUBFEED, 300KVA PP2</b>		
SIZE <b>B</b>	DWG. NO. <b>PDU56607</b>	REV <b>A</b>
PART NO.		SHEET 1 OF 1