

GENERAL SPECIFICATIONS

CABINET CHARACTERISTICS:

ENCLOSURE: NEMA 1
LOCATION: INDOOR

MECHANICAL CHARACTERISTICS

MATERIAL: STEEL
FINISH: EXTERIOR PANELS: "PEARL WHITE - PHTI-60016" OR "CARBIDE BLACK - EBT2C0000"

FRONT ACCESS FOR INSTALLATION AND MAINTENANCE
ALL OPERATOR CONTROLS ARE FRONT ACCESS WITHOUT EXPOSURE TO LIVE PARTS
MINIMUM 6" CLEARANCE FOR LEFT SIDE AND REAR FOR VENTILATION


UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
ANGULAR: $\pm 0.5^\circ$ BEND $\pm 1^\circ$
TWO PLACE DECIMAL ± 0.02
THREE PLACE DECIMAL ± 0.005

THIS DRAWING CONTAINS
CONFIDENTIAL & PROPRIETARY
INFORMATION AND SHALL NOT
BE DISCLOSED OR COPIED
WITHOUT THE EXPRESSED,
WRITTEN PERMISSION OF
POWER DISTRIBUTION, INC.



USED ON		THIRD ANGLE PROJECTION
	APPROVALS	DATE
	DRAWN	
	DESIGNED	
	CHECKED	
	ENG. APPR.	
	MFG. APPR.	

TITLE: OUTLINE PP2 300 KVA, MANUAL DUAL, 4X SQD 225A PANELBOARDS		
SIZE B	DWG. NO. PDU20625	REV
SCALE: NTS	SHEET 1 OF 2	



SIZE B	DWG. NO. PDU20625	REV
SCALE: NTS		SHEET 2 OF 2