



GENERAL SPECIFIED

CABINET CHARACTERISTIC:
ENCLOSURE : NEMA 1
LOCATION : INDOOR

MECHANICAL:
MOUNTING: BOLT TO CONCRETE FLOOR OR FLOOR STAND
MATERIAL: STEEL
WEIGHT : 3000 LBS. APPROX.

ELECTRICAL:
INPUT #1: 480 VAC 3PH W/GND @ 60 HZ, 400A (MAX) (3 EA. # 3/0-5000 MCM)
OUTPUT SUBFEED #1 - #4: 3-POLE, 208/120VAC, 100A,80% CONTINUOUS LOAD (#14 - 3/0 MCM)
OUTPUT SUBFEED #5 - #6: 3-POLE, 208/120VAC, 200A,80% CONTINUOUS LOAD (3/0 - 350 MCM)
OUTPUT SUBFEED #7 - #8: 3-POLE, 208/120VAC, 250A,80% CONTINUOUS LOAD (3/0 - 350 MCM)

ENVIROMENTAL:
OPERATING AMBIENT TEMPERATURE 0 °C TO 40 °C (32 ° F TO 104 °F)
RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING
ALTITUDE: 10,000 FT MAX

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [] IN MILLIMETER ANGULAR: ±0.5° BEND ±1° TWO PLACE DECIMAL ±0.02 THREE PLACE DECIMAL ±0.005		THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF SMITHS POWER		
 THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING		
APPROVALS		DATE		TITLE: (8) 225A SUBFEED, 400KVA PP2
DRAWN				SIZE B
CHECKED				DWG. NO. PDU56316
ENG. APPR.				REV A
		PART NO.		SHEET 1 OF 1