


High Pressure Sealing Gland For Installation with EABX-PSHP Series High Pressure Secondary Process Seal

Installation & Maintenance Information


COOPER Crouse-Hinds
IF 1477 A

SAVE THESE INSTRUCTIONS FOR FUTURE REFERENCE



INSTALLATION INSTRUCTIONS

1. Install the 3/4" male thread of the gland body into the EABX process seal hub opposite from where the high pressure is entering into the fitting. See photo to right.
2. Install union onto the conduit and cap. Insure sufficient wire is pulled to make necessary connections at junction box.
3. Feed conductors through cap, follower, insulator, sealant and second insulator up through body and into the process seal. **The open side of the pin on follower must face the cap.**
4. Carefully assemble parts into the body. Verify that the conductors are not crimped between the Body, Insulators and Follower.
5. Using a torque wrench, tighten the Cap and Body to 75 - 80 Ft-Lbs.



⚠ CAUTION

If less than 4 conductors are used, fill in the extra hole in the sealant with a 2-3" length of conductor

All statements, technical information and recommendations contained herein are based on information and tests we believe to be reliable. The accuracy or completeness thereof are not guaranteed. In accordance with Cooper Crouse-Hinds "Terms and Conditions of Sale", and since conditions of use are outside our control, the purchaser should determine the suitability of the product for his intended use and assumes all risk and liability whatsoever in connection therewith.

COOPER Crouse-Hinds

Cooper Crouse-Hinds, LLC
PO Box 4999, Syracuse, New York 13221 • U.S.A.
Copyright© 2005, Cooper Industries, Inc.

IF 1477A
Revision 1
New 02/05