


PLAN VIEW

NOTES:

1. OPERATOR INTERFACE PANEL.
2. MAIN INPUT CIRCUIT BREAKER.
3. 800A I-LINE PANEL BOARD (HCM2364-8).
4. (1-10) 50-250A SUBFEEDS.
5. (1-3) 50-250A SUBFEEDS.
6. RECOMMEND A MINIMUM OF 6" IN REAR AND LEFT SIDE OF UNIT FOR VENTILATION.
7. MINIMUM OF 36" CLEARANCE FOR DOOR SWING IN FRONT.
8. MINIMUM OF 36" CLEARANCE FOR DOOR SWING ON RIGHT SIDE.



FRONT VIEW
(DOOR AND COVERS REMOVED)

RIGHT SIDE VIEW
(DOOR AND COVERS REMOVED)

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.		-OUTLINE-			
		PDU (200-300 kVA) W/ RH 12" SIDECAR 800A I-LINE PANEL W/ (1-10) 50-250A SF & (1-3) SF IN PDU			
		DWG. NUMBER DWG11017-RH-2SF	SHEET 1 OF 1	REVISION -A-	
		DRAWN BY RAE	CHECKED BY MP	DATE 12-15-15	

