


NOTES:

1. OPERATOR INTERFACE PANEL.
2. MAIN INPUT CIRCUIT BREAKER.
3. 225A SECONDARY MAIN CIRCUIT BREAKERS.
4. (42) POLE DISTRIBUTION PANELBOARDS.
5. CT STRIP FOR BCMS (OPTIONAL).
6. (4) 150A SUBFEED BREAKERS.
7. RECOMMEND A MINIMUM OF 30" IN REAR OR SIDE OF UNIT FOR MAINTENANCE.
8. MINIMUM OF 36" CLEARANCE FOR DOOR SWING.
9. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.
10. BCMS CIRCUIT BOARD (OPTIONAL).



LEFT SIDE VIEW
(DOOR AND COVERS REMOVED)

FRONT VIEW
(DOOR AND COVERS REMOVED)

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.		TITLE		-OUTLINE-		
		PDU (200-300 kVA) W/ LH 21" SIDECAR		(4) 42P PANEL BOARDS & (4) 150A SF W/ BCMS OPTION		
		DWG. NUMBER	SHEET 1 OF 1	REVISION		
		DWG11024-23166		-A-		
DRAWN BY	LJN	CHECKED BY	RAE			
DATE	08-18-15	DATE	08-18-15			

