

Weatherproof LED luminaires

Eaton's Crouse-Hinds series LED weatherproof luminaire combines the energy efficiency of LED technology with the sharp, sleek design desired for landscaping and outdoor lighting applications. Available in gray, white and bronze, these LED luminaires provide customers with a variety of color options to help match any residential or commercial outdoor landscape.

Features:

- Durable die cast housing for long life
- Powder paint finish for corrosion resistance and pleasing appearance
- Adjustable mounting arm for directional lighting ability
- Impact-resistant lens
- Fits ½" openings of covers in 4" round and rectangular weatherproof boxes
- Voltage – 120V-277V
- Long, dependable life lasting up to 12 years
- Suitable for wet locations

Certifications and compliances:

- cULus Listed
- UL File No. E-348559


Standard material:

- Lamp head and mounting arm - die cast aluminum

Standard finish:

- Painted powder coat

Dimensions (in inches):



Cat. #	A	B	C
TPLED10B	2.75	4.92	1.57
TPLED10W	2.75	4.92	1.57
TPLED10G	2.75	4.92	1.57

Ordering Information:

Cat. #	Description	Lumens	Color temp.	Size	Unit qty.	Wt. lbs. per 100
TPLED10B	WP 10W LED LAMPHOLDER BRONZE	800	5000K	½"	4	90
TPLED10W	WP 10W LED LAMPHOLDER WHITE	800	5000K	½"	4	90
TPLED10G	WP 10W LED LAMPHOLDER GRAY	800	5000K	½"	4	90