



NOTES:

1. OPERATOR INTERFACE PANEL.
2. MAIN INPUT CIRCUIT BREAKER.
3. 225A SECONDARY MAIN CIRCUIT BREAKER.
4. (42) POLE DISTRIBUTION PANELBOARDS.
5. CT STRIP FOR BCMS (OPTIONAL).
6. (1-6) 225A SECONDARY SUBFEED BREAKER.
7. RECOMMEND A MINIMUM OF 30" IN REAR OR SIDE OF UNIT FOR MAINTENANCE.
8. MINIMUM OF 21" CLEARANCE FOR DOOR SWING.
9. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.
10. BCMS CIRCUIT BOARD (OPTIONAL).



OUTPUT CABLE AREA IN BOTTOM ONLY

FRONT VIEW
(DOOR AND COVERS REMOVED)

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.	TITLE -OUTLINE- PDU (200-300 kVA) W/ LH 21" SIDECAR (3-4) 42 P PANEL BOARDS, (1-6) 150A SF	
	DWG. NUMBER DWG11024-SO23166	1 OF 1
	DRAWN BY LJJN	REVISION
	DATE 08/18/15	-A-

