



PLAN VIEW



FRONT VIEW
(DOOR AND COVERS REMOVED)



RIGHT SIDE VIEW
(DOOR AND COVERS REMOVED)

NOTES:

1. OPERATOR INTERFACE PANEL.
2. MAIN INPUT CIRCUIT BREAKER.
3. 225A SECONDARY MAIN CIRCUIT BREAKER.
4. (42) POLE DISTRIBUTION PANELBOARDS.
5. CT STRIP FOR BCMS (OPTIONAL).
6. 1-6 (50-250A) SUBFEEDS.
7. RECOMMEND A MINIMUM OF 30" IN REAR OR SIDE OF UNIT FOR MAINTENANCE.
8. MINIMUM OF 36" CLEARANCE FOR DOOR SWING.
9. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.
10. BCMS CIRCUIT BOARD (OPTIONAL).

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.		-OUTLINE-			
		PDU (200-300 kVA) W/ RH FS SIDECAR 1-6 (50-250A) SUB FEEDS & (2) 42 POLE PANEL BOARDS			
		DWG. NUMBER	SHEET 1 OF 1	REVISION	
		DWG11168_B		-B-	
DRAWN BY	RAE	CHECKED BY	KRH		
DATE	08-05-15	DATE	08-05-15		

