

BVL – for non-armoured & SWB round cables

Technical specifications

IP54



Suitable for the following cable types



SWB - Steel wire braided cable

Steel wire braided cable to give mechanical and signal interference protection to conductors.



Non-armoured cable

Cable with insulated conductors, with no layer of mechanical (metallic) protection.

Certifications

DTCN 5975 CA

Temperature range

-40 °C to +130 °C

Material

Natural brass

Earthing washer


RM, RMC or RMF

Perfectly adapted to extreme environments

Supplied with locknut



Dimensions



Our range of MARINE BVL cable glands is a specific marine and Navy cable management solution as per DTCN 5975 CA standards.

These low-tight cable glands allow the connection of non-armoured, and steel wire braided armoured cables.

Made of natural brass, the cable glands accommodate a locknut and achieve a perfect tensile strength as well as an IP54.

With an operating temperature range starting from -40°C up to +130°C, the BVL range meets the requirement for cable entries management in marine environments.

Ordering codes

Size	Cable Diameter		A	Thread (B) / Pitch	C	L	E	Catalog Number
	External	Under Armour						
1	14.0	12.0	24.0	17.0 x 1.5	25.0	35.5	12.0	CAP539100
2	16.5	14.5	27.0	20.0 x 1.5	28.0	35.5	12.0	CAP539200
3	20.5	19.0	32.0	24.0 x 1.5	32.0	35.5	12.0	CAP539300
4	25.0	22.5	36.0	28.0 x 1.5	36.0	35.5	12.0	CAP539400
5	30.0	28.0	42.0	35.0 x 1.5	42.0	35.5	12.0	CAP539500
6	39.0	36.0	55.0	44.0 x 2.0	55.0	35.5	12.0	CAP539600
7	44.5	42.5	60.0	50.0 x 2.0	60.0	35.5	12.0	CAP539700

All dimensions in mm.