



NOTES:


1. OPERATOR INTERFACE PANEL.
2. MAIN INPUT CIRCUIT BREAKER.
3. 225A SECONDARY MAIN CIRCUIT BREAKER.
4. 225A (42) POLE DISTRIBUTION PANELBOARD.
5. 225AF SUBFEED BREAKER.
6. RECOMMEND A MINIMUM OF 30" IN REAR OF UNIT FOR MAINTENANCE.
7. MINIMUM OF 18" CLEARANCE FOR DOOR SWING IN FRONT.
8. MINIMUM OF 32" CLEARANCE FOR DOOR SWING ON SIDES.
9. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.



LEFT SIDE VIEW
(DOOR AND COVERS REMOVED)



FRONT VIEW
(DOOR AND COVERS REMOVED)



RIGHT SIDE VIEW
(DOOR AND COVERS REMOVED)

OUTPUT CABLE AREA IN BOTTOM ONLY

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.

TITLE		-OUTLINE-	
PDU (300 kVA)		W/ (x2) 9" SIDECARS	
(4) 225A 42P PANEL BOARDS & (1-4) 225 AF SUBFEEDS			
DWG. NUMBER	1 OF 1		
	DWG11175		
DRAWN BY	RAE	REVISION	
DATE	06-02-10	-A-	

