


NOTES:

1. OPERATOR INTERFACE PANEL.
2. DUAL MAIN INPUT BREAKERS (WITH KIRK KEY).
3. SOLENOID KEY RELEASE.
4. 400A SUBFEEDS.
5. 800A I-LINE PANEL BOARD WITH (10) 225A SUB FEED.
6. BCMS MODULAR.
7. RECOMMEND A MINIMUM OF 30" IN REAR OR SIDE .
8. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.
9. MINIMUM OF 21" CLEARANCE FOR DOOR SWING.
10. UNIT CONFIG FOR BOTTOM ENTRY AND EXIT.



(DOOR AND COVERS REMOVED)

<p>THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.</p>	<p>TITLE -OUTLINE-</p> <p>MDP POWERPAK PDU 200-300kVA 400A SF, 800A I-LINE PANEL BOARD, W/ BCMS</p>	
	<p>DWG. NUMBER</p> <p>MDP18764</p>	<p>1 OF 1</p>
	<p>DRAWN BY</p> <p>LJN</p>	<p>REVISION</p> <p>-A-</p>
	<p>DATE</p> <p>7/31/15</p>	

