




NOTES:


1. OPERATOR INTERFACE PANEL.
2. MAIN INPUT CIRCUIT BREAKER.
3. 225A SECONDARY MAIN CIRCUIT BREAKER.
4. (42) POLE DISTRIBUTION PANELBOARDS.
5. CT STRIP FOR BCMS (OPTIONAL).
6. RECOMMEND A MINIMUM OF 30" IN REAR OF UNIT FOR MAINTENANCE.
7. MINIMUM OF 21" CLEARANCE FOR DOOR SWING.
8. RECOMMEND 6" CLEARANCE BETWEEN VENTILATED SIDES AND WALL FOR PROPER COOLING.
9. BCMS CIRCUIT BOARD (OPTIONAL).



FRONT VIEW
(DOOR AND COVERS REMOVED)



RIGHT SIDE VIEW
(DOOR AND COVERS REMOVED)

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION INC.		-OUTLINE-	
		PDU (30-150 kVA) , 21" RH SIDE CARR	
		(4) 42 POLE PANEL BOARDS WITH BCMS OPTION, (2) SF	
		DWG. NUMBER 1 OF 1 PDU18193	
DRAWN BY LJN	REVISION	 creating the perfect wave	
DATE 04/09/15	-A-		