



GENERAL SPECIFIED

CABINET CHARACTERISTIC: DOOR AND PANELS REMOVED
 ENCLOSURE : NEMA 1
 LOCATION : INDOOR

MECHANICAL:
 MATERIAL: STEEL
 FINISH: EXTERIOR PANELS: PEARL WHITE - PHTI-60016
 WEIGHT : 600 LBS. APPROX.

ELECTRICAL:
 INPUT #1: 208 VAC 3PH-4W W/GND @ 60 HZ, 225A (MAX) (2 EA. # 2/O-350 MCM CU)
 INPUT #2: 208 VAC 3PH-4W W/GND @ 60 HZ, 225A (MAX) (2 EA. # 2/O-350 MCM CU)
 OUTPUT PB #1: 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)
 OUTPUT PB #2: 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)

ENVIRONMENTAL:
 OPERATING AMBIENT TEMPERATURE 0 °C to 40 °C (32 ° F to 104 °F)
 RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING
 ALTITUDE: 10,000 FT MAX

FRONT VIEW

**SIDE VIEW
 PANEL REMOVED**

**REAR VIEW
 PANEL REMOVED**

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: ANGULAR: ±0.5° BEND±1° TWO PLACE DECIMAL ±0.02 THREE PLACE DECIMAL ±0.005		THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF POWER DISTRIBUTION, INC.			
USED ON		 DO NOT SCALE DRAWING			
		APPROVALS		TITLE:	
		DRAWN ISF		ABB MLO, (2) PANEL BOARD RPP	
MATERIAL: NA		CHECKED LJN		DATE 5/19/15	
FINISH: NA		ENG. APPR.		SCALE: 1:24	
WEIGHT:				SHEET 1 OF 1	
				PART NO.	
				SIZE DWG. NO. REV B rpp18397 B	