

**NmRBM: Influence of ambient temperature on load carrying capacity**

- Values = max. allowed current in Ampere at the specific temperature
- Temperature factor (%/K) = 0.5

$I_n$ [A]	Ambient temperature / °C										
	-40	-30	-25	-20	-10	0	10	20	30	40	
6	8.1	7.8	7.7	7.5	7.2	6.9	6.6	6.3	6.0	5.7	
10	13.5	13.0	12.8	12.5	12.0	11.5	11.0	10.5	10.0	9.5	
13	17.6	16.9	16.6	16.3	15.6	15.0	14.3	13.7	13.0	12.4	
15-OL	20.0	19.3	18.9	18.6	17.9	17.1	16.4	15.7	15.0	14.3	
16	21.6	20.8	20.4	20.0	19.2	18.4	17.6	16.8	16.0	15.2	
20	27.0	26.0	25.5	25.0	24.0	23.0	22.0	21.0	20.0	19.0	
20-OL	26.7	25.7	25.2	24.8	23.8	22.5	21.9	21.0	20.0	19.0	

**NmRB6: Influence of ambient temperature on load carrying capacity**

- Values = max. allowed current in Ampere at the specific temperature
- Temperature factor (%/K) = 0.5

$I_n$ [A]	Ambient temperature / °C										
	-40	-30	-25	-20	-10	0	10	20	30	40	
25	33.8	32.5	31.9	31.3	30.0	28.8	27.5	26.3	25.0	23.8	
32	43.2	41.6	40.8	40.0	38.4	36.8	35.2	33.6	32.0	30.4	
40	54.0	52.0	51.0	50.0	48.0	46.0	44.0	42.0	40.0	38.0	