



GENERAL SPECIFIED

CABINET CHARACTERISTIC:
 ENCLOSURE : NEMA 1
 LOCATION : INDOOR

MECHANICAL:
 MATERIAL: STEEL
 FINISH: EXTERIOR PANELS: PEARL WHITE - PHTI-60016
 WEIGHT : 600 LBS. APPROX.

ELECTRICAL:
 INPUT #1: 208 VAC 3PH-4W W/GND @ 60 HZ, 225A (MAX) (2 EA. # 2/O-350 MCM CU)
 INPUT #2: 208 VAC 3PH-4W W/GND @ 60 HZ, 225A (MAX) (2 EA. # 2/O-350 MCM CU)
 OUTPUT PB #1: 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)
 OUTPUT PB #2: 42 POLE, BOLT ON CIRCUIT BREAKER (60 A MAX)

ENVIROMENTAL:
 OPERATING AMBIENT TEMPERATURE 0 °C TO 40 °C (32 ° F TO 104 °F)
 RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING
 ALTITUDE: 10,000 FT MAX

FRONT VIEW
 DOOR AND PANELS REMOVED

SIDE VIEW
 PANEL REMOVED

REAR VIEW
 PANEL REMOVED

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN INCHES
 TOLERANCES:
 ANGULAR: ±0.5° BEND ±1°
 TWO PLACE DECIMAL ±0.02
 THREE PLACE DECIMAL ±0.005

THIS DRAWING CONTAINS
 CONFIDENTIAL & PROPRIETARY
 INFORMATION AND SHALL NOT
 BE DISCLOSED OR COPIED
 WITHOUT THE EXPRESSED,
 WRITTEN PERMISSION OF
 POWER DISTRIBUTION, INC.



USED ON	DO NOT SCALE DRAWING	
APPROVALS		DATE
DRAWN	ISF	5/19/15
MATERIAL: NA	CHECKED	LJN
FINISH: NA	ENG. APPR.	5/19/15
WEIGHT:		

TITLE: ABB MLO, (2) PANEL BOARD RPP		
SIZE B	DWG. NO. RPP18554	REV A
SCALE: 1:24	PART NO.	SHEET 1 OF 1